


ET S7-400-GE-A4-3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration



The ET S7 DIN-A4 non-adhesive labels are used to label the S300, S400 and S7 modules from Siemens. Customised laser printing is possible using Weidmüller's M-Print® Pro software.

- Background colours yellow or turquoise with black printing (boxes)
- Labels can be easily separated (not adhesive)

General ordering data

Version	LaserMark, Device markers, 251 x 13.5 mm, Siemens, yellow
Order No.	1847640000
Type	ET S7-400-GE-A4-3
GTIN (EAN)	4032248366354
Qty.	10 items
Delivery status	Discontinued
Available until	2024-05-30T00:00:00+02:00

ET S7-400-GE-A4-3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.1 mm	Depth (inches)	0.0039 inch
Height	251 mm	Height (inches)	9.8819 inch
Width	13.5 mm	Width (inches)	0.5315 inch
Net weight	30.1 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Material colour according to resistance code	4	
Number per sheet	14	
Printing method	Laser print	
Width	13.5 mm	
UL 94 flammability rating	HB	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-40 °C	
Colour	yellow	
Halogen	Yes	
Basic material	Vinyl film	
Number of markers per packaging unit	140	
Number of markers per packaging unit	Form of supply	Label sheet
	Number of combinations per packaging unit	10
	Number of markers per combination	14
Approval acc. to UL 969 compatible printer	No	
Number of markers per combination	1 Label sheet = 14 Device markers	
Operating temperature range	-40...80 °C	
Application/manufacturer	Siemens	

Device markers

Halogen	Yes
---------	-----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

