

SAISGI-P-4A-5.5/8-M12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems. The IDC is simple and quick to assemble since this technology allows the conductor to be inserted directly into the terminal point, without crimping or having to strip the insulation. It also has excellent functional security.

General ordering data

Version	Field attachable connector, M12
Order No.	1852740000
Type	SAISGI-P-4A-5.5/8-M12
GTIN (EAN)	4032248386864
Qty.	1 items

SAISGI-P-4A-5.5/8-M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Diameter	20.5 mm	Net weight	34 g
----------	---------	------------	------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical data customisable plug-in connectors

Number of poles	4	Coding	A-coded
Contact surface	tinned	LED	No
Type of connection	Insulation displacement connection	Housing main material	CuZn
Insulation resistance	108 Ω	Cable diameter, max.	8 mm
Cable diameter, min.	5.5 mm	Contact material	Copper alloy
Conductor cross-section, max.	0.75 mm ²	Conductor cross-section, min.	0.34 mm ²
Nominal voltage	50 V	Nominal current	6 A
Protection degree	IP67	Plugging cycles	≥ 50
Pollution severity	3	Gender of contact	Male
Shield connection	No	Threaded ring material	Diecast zinc
Temperature range of housing	-25...+85 °C		

General Info

Number of poles	4	Connection 1	M12
Connection 2	IDC	Description of article	SAIS / B IDC (0.75)
UL 94 flammability rating	V-0	Housing main material	CuZn
Connection thread	M12	Contact material	Copper alloy
Contact surface	tinned	Wire connection cross section, finely stranded, min.	0.34 mm ²
Wire connection cross section, finely stranded, max.	0.75 mm ²	Protection degree	IP67
Plugging cycles	≥ 50		

Standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

Pole scheme

