

ZP 4/1AN/4

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

General ordering data

Version	Z-series, Plug-in connector, beige, Direct mounting
Order No.	1855010000
Type	ZP 4/1AN/4
GTIN (EAN)	4032248396085
Qty.	25 items

Technical data**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E60693

Dimensions and weights

Depth	47.5 mm	Depth (inches)	1.8701 inch
Height	22.5 mm	Height (inches)	0.8858 inch
Width	26 mm	Width (inches)	1.0236 inch
Net weight	22.27 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...75 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	Set of connectors, pluggable, Tension-clamp connection	End cover plate required	No
Number of potentials	4	Number of levels	1
Number of clamping points per level	1	Levels cross-connected internally	No
PE connection	No		

Additional technical data

Open sides	closed	Installation advice	Direct mounting
Type of mounting	Plugged		

CSA rating data

Wire cross section max. (CSA)	10 AWG	Voltage size C (CSA)	600 V
Current size C (CSA)	28 A	Certificate No. (CSA)	200039-1720292
Wire cross section min. (CSA)	26 AWG		

Conductors for clamping (rated connection)

Gauge to IEC 60947-1	A3
Wire connection cross section AWG, max.	AWG 10

Technical data

Connection direction	top																		
Stripping length	12 mm																		
Type of connection	Tension-clamp connection																		
Number of connections	4																		
Clamping range, max.	6 mm ²																		
Clamping range, min.	0.13 mm ²																		
Blade size	0.6 x 3.5 mm																		
Wire connection cross section AWG, min.	AWG 26																		
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.13 mm ²																		
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	4 mm ²																		
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.13 mm ²																		
Wire connection cross section, finely stranded, max.	6 mm ²																		
Wire connection cross section, finely stranded, min.	0.13 mm ²																		
Connection cross-section, stranded, min.	0.13 mm ²																		
Wire connection cross-section, solid core, max.	6 mm ²																		
Wire connection cross-section, solid core, min.	0.13 mm ²																		
Tube length for wire-end ferrule with plastic collar DIN 46228/4	<table border="1"> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.5 mm²</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.75 mm²</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1 mm²</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1.5 mm²</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>2.5 mm²</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>4 mm²</td> </tr> </table>	Cross-section for conductor connection	nominal	0.5 mm ²	Cross-section for conductor connection	nominal	0.75 mm ²	Cross-section for conductor connection	nominal	1 mm ²	Cross-section for conductor connection	nominal	1.5 mm ²	Cross-section for conductor connection	nominal	2.5 mm ²	Cross-section for conductor connection	nominal	4 mm ²
Cross-section for conductor connection	nominal	0.5 mm ²																	
Cross-section for conductor connection	nominal	0.75 mm ²																	
Cross-section for conductor connection	nominal	1 mm ²																	
Cross-section for conductor connection	nominal	1.5 mm ²																	
Cross-section for conductor connection	nominal	2.5 mm ²																	
Cross-section for conductor connection	nominal	4 mm ²																	
Tube length for twin wire-end ferrule	<table border="1"> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.5 mm²</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.75 mm²</td> </tr> </table>	Cross-section for conductor connection	nominal	0.5 mm ²	Cross-section for conductor connection	nominal	0.75 mm ²												
Cross-section for conductor connection	nominal	0.5 mm ²																	
Cross-section for conductor connection	nominal	0.75 mm ²																	
Tube length for wire-end ferrule without plastic collar DIN 46228/1	<table border="1"> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.5 mm²</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.75 mm²</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1 mm²</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1.5 mm²</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>2.5 mm²</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>4 mm²</td> </tr> </table>	Cross-section for conductor connection	nominal	0.5 mm ²	Cross-section for conductor connection	nominal	0.75 mm ²	Cross-section for conductor connection	nominal	1 mm ²	Cross-section for conductor connection	nominal	1.5 mm ²	Cross-section for conductor connection	nominal	2.5 mm ²	Cross-section for conductor connection	nominal	4 mm ²
Cross-section for conductor connection	nominal	0.5 mm ²																	
Cross-section for conductor connection	nominal	0.75 mm ²																	
Cross-section for conductor connection	nominal	1 mm ²																	
Cross-section for conductor connection	nominal	1.5 mm ²																	
Cross-section for conductor connection	nominal	2.5 mm ²																	
Cross-section for conductor connection	nominal	4 mm ²																	

General

Number of poles	4	Wire connection cross section AWG, max.	AWG 10
Installation advice	Direct mounting	Wire connection cross section AWG, min.	AWG 26
Standards	In accordance with IEC 60947-7-1		

Rating data

Rated cross-section	4 mm ²	Rated voltage	800 V
Rated DC voltage	800 V	Nominal current	32 A
Current at maximum wires	32 A	Standards	In accordance with IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	1 mΩ	Rated impulse withstand voltage	8 kV

Technical data

Power loss in accordance with IEC 60947-7-x	1.02 W	Pollution severity	3
---	--------	--------------------	---

UL rating data

Conductor size Factory wiring max. (cURus)	10 AWG	Certificate No. (cURus)	E60693
Conductor size Field wiring min. (cURus)	26 AWG	Conductor size Factory wiring min. (cURus)	26 AWG
Voltage size C (cURus)	600 V	Current size C (cURus)	28 A
Conductor size Field wiring max. (cURus)	10 AWG		

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

Accessories

Plugs



The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

General ordering data

Type	ZVR ZP4	Version
Order No.	1855250000	Z-series, Locking clips, Direct mounting
GTIN (EAN)	4032248396481	
Qty.	25 ST	
Type	KOSF ZT4	Version
Order No.	1856860000	Z-series, Coding element, Direct mounting
GTIN (EAN)	4032248400744	
Qty.	50 ST	
Type	ZZE ZP4	Version
Order No.	1855260000	Z-series, Strain relief, Direct mounting
GTIN (EAN)	4032248396498	
Qty.	25 ST	

Slotted screwdriver



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

General ordering data

Type	SDS 0.6X3.5X100	Version
Order No.	9008330000	Screwdriver, Screwdriver
GTIN (EAN)	4032248056286	
Qty.	1 ST	

ZP 4/1AN/4

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	DEK 5/6 MC NE WS	Version
Order No.	1609820000	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4008190203436	Weidmüller, white
Qty.	1000 ST	
Type	WS 10/6 M MC NE WS	Version
Order No.	1818400000	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmüller,
GTIN (EAN)	4032248310876	Allen-Bradley, white
Qty.	600 ST	
Type	WS 10/6 MC NE WS	Version
Order No.	1828450000	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmüller,
GTIN (EAN)	4032248350513	Allen-Bradley, white
Qty.	600 ST	

Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

General ordering data

Type	BZT 1 WS 10/5	Version
Order No.	1805490000	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 ST	
Type	BZT 1 ZA WS 10/5	Version
Order No.	1805520000	Accessories, Marker holder
GTIN (EAN)	4032248270248	
Qty.	100 ST	

ZP 4/1AN/4

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

DEK 5/6



WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

Type	DEK 5/6 MM WS	Version
Order No.	2007120000	Dekafix, Terminal marker, 5 x 6 mm, Weidmueller, white
GTIN (EAN)	4050118392104	
Qty.	600 ST	