


SAIE-M12B-4-0.5U-FP-M16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Version	Built-in plugs, M12, Female socket, straight, Mounting thread: M 16 x 1.5, Number of poles: 4, Strand / cable length: 0.5 m, Front mounting
Order No.	1861190000
Type	SAIE-M12B-4-0.5U-FP-M16
GTIN (EAN)	4032248419265
Qty.	1 items

SAIE-M12B-4-0.5U-FP-M16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E307231

Dimensions and weights

Net weight	16.65 g
------------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical specifications for cable

PE function	No	Core cross-section	0.34 mm ²
Wire cross section (Print/Online)	0.34 (4- and 5-pole)/ 0.25 (8-pole)/ 0.14 (12-pole)	Strand / cable length	0.5 m
Colour coding	brown, white, blue, black	Number of poles	4

Technical data customisable plug-in connectors

Number of poles	4	Coding	A-coded
Contact surface	Gold-plated	Housing main material	Zinc diecast
Nominal voltage	250 V	Nominal current	4 A
Protection degree	IP67, when screwed in	Plugging cycles	≥ 100
Rated current	4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole)	Temperature range of housing	-30...+90 °C

Standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

General data

Number of poles	4
Coding	A-coded
Connection thread	M12
Contact surface	Gold-plated
Tightening torque	1 Nm
Core cross-section	0.34 mm ²
Housing main material	Zinc diecast
Type of mounting	Front mounting
Nominal voltage	250 V
Nominal current	4 A
Protection degree	IP67, when screwed in
Plugging cycles	≥ 100
Basic material	PVC
Rated voltage	250 V (4-pole)/ 60 V (5-pole)/ 30 V (8 and 12-pole)

SAIE-M12B-4-0.5U-FP-M16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Rated current	4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole)		
Wire cross section (Print/Online)	0.34 (4- and 5-pole)/ 0.25 (8-pole)/ 0.14 (12-pole)		
Connection 1	M12		
Connection 2	Flying wires		
Strand / cable length	0.5 m		
Mounting thread	M 16 x 1.5		
Mounting torque range	2 Nm		
Mounting torque	max.	2 Nm	
Temperature range of housing	-30...+90 °C		
Conductor O.D.	-		

Classifications

ETIM 8.0	EC003570	ETIM 9.0	EC003570
ETIM 10.0	EC003570	ECLASS 14.0	27-44-01-03
ECLASS 15.0	27-44-01-03		

Wiring diagram



Pole scheme

