

**ZVLA SC ZPS2.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

**General ordering data**

Version	Z-series, Plug-in modular terminals, yellow, 15 mm
Order No.	<a href="#">1866240000</a>
Type	ZVLA SC ZPS2.5
GTIN (EAN)	4032248513376
Qty.	20 items

## ZVLA SC ZPS2.5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	26 mm	Depth (inches)	1.0236 inch
Height	73.8 mm	Height (inches)	2.9055 inch
Width	15 mm	Width (inches)	0.5906 inch
Net weight	5 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	PA 66 GF 30	Colour	yellow
UL 94 flammability rating	HB		

### System specifications

Version	Intermediate part
---------	-------------------

### Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

### Conductors for clamping (rated connection)

Type of connection	Plug-in connection	Number of connections	0
--------------------	--------------------	-----------------------	---

### General

Number of poles	1	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

### Rating data

Rated cross-section	2.5 mm <sup>2</sup>
---------------------	---------------------

### Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		