

## CLI C 02-3 WS/SW 6 CD

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

|            |   |
|------------|---|
| Version    | CableLine, Conductor and cable markers, 1.3 - 3 mm, 3 x 3.4 mm, white |
| Order No.  | <a href="#">1869821520</a>  |
| Type       | CLI C 02-3 WS/SW 6 CD   |
| GTIN (EAN) | 4032248446407   |
| Qty.       | 500 items   |

**CLI C 02-3 WS/SW 6 CD**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 3.5 mm | Depth (inches)  | 0.1378 inch |
| Height     | 3 mm   | Height (inches) | 0.1181 inch |
| Width      | 3.4 mm | Width (inches)  | 0.1339 inch |
| Net weight | 0.04 g |                 |             |

**Temperatures**

Operating temperature range -30...80 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

|  |                                      |      |  |
|--|--------------------------------------|------|--|
| Material colour according to resistance code | 9                                    |      |  |
| Orientation of print                         | horizontal                           |      |  |
| Type of printing                             | Standard                             |      |  |
| Printing method                              | hot-embossing                        |      |  |
| Version                                      | CD                                   |      |  |
| Width  | 3.4 mm                               |      |  |
| UL 94 flammability rating                    | V-0                                  |      |  |
| Operating temperature range, max.            | 80 °C                                |      |  |
| Operating temperature range, min.            | -30 °C                               |      |  |
| Colour                                       | white                                |      |  |
| Halogen                                      | Yes                                  |      |  |
| Basic material                               | PVC, soft, without Cadmium           |      |  |
| Colour of printing                           | black                                |      |  |
| Printed characters                           | Numbers                              |      |  |
| Number of markers per packaging unit         | Form of supply                       | Reel |  |
| Recommended industries                       | Process, Machinery                   |      |  |
| Number of markers per combination            | 1 Reel = Conductor and cable markers |      |  |
| Operating temperature range                  | -30...80 °C                          |      |  |
| Imprint                                      | 6                                    |      |  |

**Conductor and cable markers**

|                                  |                           |                               |                     |
|----------------------------------|---------------------------|-------------------------------|---------------------|
| Halogen                          | Yes                       | Conductor cross-section, max. | 1.5 mm <sup>2</sup> |
| Conductor cross-section, min.    | 0.2 mm <sup>2</sup>       | Conductor O.D., max.          | 3 mm                |
| Conductor O.D., min.             | 1.3 mm                    | Conductor O.D.                | 1.3 - 3 mm          |
| Cross-section for connected wire | 0.2 - 1.5 mm <sup>2</sup> |                               |                     |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**



Similar to illustration