

CLI C 02-6 SDR CD


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Version	CableLine, Conductor and cable markers, 1.3 - 3 mm, 6 x 3.4 mm, To customer specification
Order No.	186999999
Type	CLI C 02-6 SDR CD
GTIN (EAN)	4032248457403
Qty.	250 items

CLI C 02-6 SDR CD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	3.5 mm	Depth (inches)	0.1378 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	3.4 mm	Width (inches)	0.1339 inch
Net weight	0.11 g		

Temperatures

Operating temperature range -30...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Orientation of print	horizontal	Type of printing	To customer specification
Printing method	Ink jet technology	Version	CD
Width	3.4 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Colour	To customer specification	Halogen	Yes
Basic material	PVC, soft, without Cadmium	Colour of printing	black
Printed characters	To customer specification	Operating temperature range	-30...80 °C
Imprint	Custom printing		

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.2 mm ²	Conductor O.D., max.	3 mm
Conductor O.D., min.	1.3 mm	Conductor O.D.	1.3 - 3 mm
Cross-section for connected wire	0.2 - 1.5 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings



Similar to illustration