

SAISGI-M-2B-4.5/8.8-M12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The IDC is simple and quick to assemble since this technology allows the conductor to be inserted directly into the terminal point, without crimping or having to strip the insulation. It also has excellent functional security.

General ordering data

Version	Field attachable connector, M12
Order No.	1864730000
Type	SAISGI-M-2B-4.5/8.8-M12
GTIN (EAN)	4032248430543
Qty.	1 items

SAISGI-M-2B-4.5/8.8-M12

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	50 g
------------	------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical data customisable plug-in connectors

Number of poles	2	Coding	B-coded
Contact surface	tinned	Assignment	Pin 2 + Pin 4
Type of connection	Insulation displacement connection	Housing main material	CuZn
Insulation resistance	108 Ω	Cable diameter, max.	8.8 mm
Cable diameter, min.	4.5 mm	Conductor cross-section, max.	0.34 mm ²
Conductor cross-section, min.	0.25 mm ²	Nominal voltage	32 V
Nominal current	4 A	Protection degree	IP67
Plugging cycles	≥ 50	Pollution severity	3
Gender of contact	Male	Shield connection	Yes
Threaded ring material	Diecast zinc	Temperature range of housing	-25...+85 °C

General Info

Number of poles	2	Connection 1	M12
Connection 2	IDC	Housing main material	CuZn
Connection thread	M12	Contact surface	tinned
Protection degree	IP67	Plugging cycles	≥ 50

Standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 9.0	27-44-01-02
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-02
ECLASS 11.0	27-44-01-02	ECLASS 12.0	27-44-01-16
ECLASS 13.0	27-44-01-02	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

Pole scheme