



Our extensive range of TM sleeves is suitable for all-purpose use. They cover a wide range of applications: from thin conductors to cables with large external diameters. This range offers printed inlay tags with maximum protection against outside influences. TM sleeves permit flexible installation.

- Optimum protection for printed inlay tags
- Wide range of applications for conductors and cables
- One tag type for all cross-sections
- TMX 30 for mounting with cable ties (width 4.6 mm)

### General ordering data

Version	TM, Socket x 20 mm, PVC, Colour: Transparent, Conductor O.D.: 10 - 317 mm
Order No.	<a href="#">1866680000</a>
Type	TMX 30 V0
GTIN (EAN)	4032248436958
Qty.	400 items

**TMX 30 V0**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Height	30 mm	Height (inches)	1.1811 inch
Width	20 mm	Width (inches)	0.7874 inch
Net weight	0.62 g		

**Temperatures**

Operating temperature range -40...80 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Type of printing	neutral	Width	20 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Colour	Transparent
Basic material	PVC	Recommended industries	Transportation, Machinery
Operating temperature range	-40...80 °C		

**Conductor and cable markers**

Conductor cross-section, max.	150 mm <sup>2</sup>	Conductor cross-section, min.	16 mm <sup>2</sup>
Conductor O.D., max.	317 mm	Conductor O.D., min.	10 mm
Conductor O.D.	10 - 317 mm	Cross-section for connected wire	16 - 150 mm <sup>2</sup>

**Classifications**

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**

