

**ZP 2.5/1AN/5 GN/BE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

**General ordering data**

Version	Z-series, Plug-in connector, beige, Direct mounting
Order No.	<a href="#">1867120000</a>
Type	ZP 2.5/1AN/5 GN/BE
GTIN (EAN)	4032248475650
Qty.	25 items

## ZP 2.5/1AN/5 GN/BE

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

## Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURus)	E60693

## Dimensions and weights

Depth	41 mm	Depth (inches)	1.6142 inch
Height	16 mm	Height (inches)	0.6299 inch
Width	25.5 mm	Width (inches)	1.0039 inch
Net weight	16.12 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...75 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

## System specifications

Version	Set of connectors, pluggable, Tension-clamp connection	End cover plate required	No
Number of potentials	5	Number of levels	1
Number of clamping points per level	1	Levels cross-connected internally	No
PE connection	Yes		

## Additional technical data

Open sides	closed	Installation advice	Direct mounting
Type of mounting	Plugged		

## CSA rating data

Voltage size C (cCSAus)	300 V	Current size D (cCSAus)	5 A
Wire cross section min. (cCSAusX)	26 AWG	Current size C (cCSAus)	20 A
Certificate number (cCSAus)	154685-1460993	Wire cross section max. (cCSAusX)	12 AWG
Voltage size D (cCSAus)	600 V		

## Conductors for clamping (rated connection)

Gauge to IEC 60947-1	A2
----------------------	----

## ZP 2.5/1AN/5 GN/BE

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Wire connection cross section AWG, max.	AWG 12															
Connection direction	top															
Stripping length	10 mm															
Type of connection	Plug-in connection															
Number of connections	5															
Clamping range, max.	4 mm <sup>2</sup>															
Clamping range, min.	0.13 mm <sup>2</sup>															
Blade size	0.6 x 3.5 mm															
Wire connection cross section AWG, min.	AWG 12															
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.13 mm <sup>2</sup>															
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	2.5 mm <sup>2</sup>															
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.13 mm <sup>2</sup>															
Wire connection cross section, finely stranded, max.	4 mm <sup>2</sup>															
Wire connection cross section, finely stranded, min.	0.13 mm <sup>2</sup>															
Connection cross-section, stranded, min.	0.13 mm <sup>2</sup>															
Wire connection cross-section, solid core, max.	4 mm <sup>2</sup>															
Wire connection cross-section, solid core, min.	0.13 mm <sup>2</sup>															
Tube length for wire-end ferrule with plastic collar DIN 46228/4	<table border="1"> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.5 mm<sup>2</sup></td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.75 mm<sup>2</sup></td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1 mm<sup>2</sup></td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1.5 mm<sup>2</sup></td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>2.5 mm<sup>2</sup></td> </tr> </table>	Cross-section for conductor connection	nominal	0.5 mm <sup>2</sup>	Cross-section for conductor connection	nominal	0.75 mm <sup>2</sup>	Cross-section for conductor connection	nominal	1 mm <sup>2</sup>	Cross-section for conductor connection	nominal	1.5 mm <sup>2</sup>	Cross-section for conductor connection	nominal	2.5 mm <sup>2</sup>
Cross-section for conductor connection	nominal	0.5 mm <sup>2</sup>														
Cross-section for conductor connection	nominal	0.75 mm <sup>2</sup>														
Cross-section for conductor connection	nominal	1 mm <sup>2</sup>														
Cross-section for conductor connection	nominal	1.5 mm <sup>2</sup>														
Cross-section for conductor connection	nominal	2.5 mm <sup>2</sup>														
Tube length for wire-end ferrule without plastic collar DIN 46228/1	<table border="1"> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.5 mm<sup>2</sup></td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.75 mm<sup>2</sup></td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1 mm<sup>2</sup></td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1.5 mm<sup>2</sup></td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>2.5 mm<sup>2</sup></td> </tr> </table>	Cross-section for conductor connection	nominal	0.5 mm <sup>2</sup>	Cross-section for conductor connection	nominal	0.75 mm <sup>2</sup>	Cross-section for conductor connection	nominal	1 mm <sup>2</sup>	Cross-section for conductor connection	nominal	1.5 mm <sup>2</sup>	Cross-section for conductor connection	nominal	2.5 mm <sup>2</sup>
Cross-section for conductor connection	nominal	0.5 mm <sup>2</sup>														
Cross-section for conductor connection	nominal	0.75 mm <sup>2</sup>														
Cross-section for conductor connection	nominal	1 mm <sup>2</sup>														
Cross-section for conductor connection	nominal	1.5 mm <sup>2</sup>														
Cross-section for conductor connection	nominal	2.5 mm <sup>2</sup>														

## General

Number of poles	5	Wire connection cross section AWG, max.	AWG 12
Installation advice	Direct mounting	Wire connection cross section AWG, min.	AWG 12
Standards	In accordance with IEC 60947-7-1		

## Rating data

Rated cross-section	2.5 mm <sup>2</sup>	Rated voltage	500 V
Rated voltage to adjoining terminal	500 V	Max. voltage of clamp support & pluggable system	690 V
Rated DC voltage	500 V	Nominal current	24 A
Current at maximum wires	24 A	Standards	In accordance with IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	1.33 mΩ	Rated impulse withstand voltage	6 kV
Rated impulse withstand voltage to adjacent terminal	6 kV	Power loss in accordance with IEC 60947-7-x	0.77 W

**ZP 2.5/1AN/5 GN/BE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****UL rating data**

Conductor size Factory wiring max. (cURus)	12 AWG
Certificate No. (cURus)	E60693
Conductor size Factory wiring min. (cURus)	26 AWG
Current size C (cURus)	20 A
Conductor size Field wiring max. (cURus)	12 AWG

Voltage size D (cURus)	600 V
Conductor size Field wiring min. (cURus)	26 AWG
Voltage size C (cURus)	300 V
Current size D (cURus)	5 A

**Classifications**

ETIM 8.0	EC002848
ETIM 10.0	EC002848
ECLASS 15.0	27-25-03-90

ETIM 9.0	EC002848
ECLASS 14.0	27-25-03-90

## ZP 2.5/1AN/5 GN/BE

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Testadapter and testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

Type	ZTA ZT2.5	Version
Order No.	<a href="#">1827080000</a>	Accessories, Test adapter, 17.5 A
GTIN (EAN)	4032248411276	
Qty.	25 ST	
Type	ZTA ZT2.5/ZA	Version
Order No.	<a href="#">1847600000</a>	Accessories, Test adapter, 17.5 A
GTIN (EAN)	4032248412679	
Qty.	25 ST	

## Slotted screwdriver



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

## General ordering data

Type	SDS 0.6X3.5X100	Version
Order No.	<a href="#">9008330000</a>	Screwdriver, Screwdriver
GTIN (EAN)	4032248056286	
Qty.	1 ST	


## ZP 2.5/1AN/5 GN/BE

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/5 MC NE BL	Version
Order No.	<a href="#">1609801693</a>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190397166	Weidmüller, blue
Qty.	1000 ST	

## STR transparent strips



## General ordering data

Type	STR 7 F.SCHT 7	Version
Order No.	<a href="#">0515300000</a>	Terminal markers, Protective cap, 27 x 6.3 mm, Transparent
GTIN (EAN)	4008190182175	
Qty.	20 ST	


## ZP 2.5/1AN/5 GN/BE

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Blank



ZS markers - in proven MultiCard-format - have been developed specifically for the Z-series. They have a large printing area. The hinged mechanism even allows access to cross-connectors without dismantling. Quick installation is guaranteed by the fact that the single tags are clipped on in strips. The single tags are easy to separate.

- Hinged marker area
- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	ZS 10/5 MC NE WS	Version
Order No.	<a href="#">1610000000</a>	ZS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmüller,
GTIN (EAN)	4008190263171	Allen-Bradley, white
Qty.	480 ST	
Type	WS 10/5 M MC NE WS	Version
Order No.	<a href="#">1792000000</a>	WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmüller,
GTIN (EAN)	4032248223862	Allen-Bradley, white
Qty.	720 ST	

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

Type	BZT 1 WS 10/5	Version
Order No.	<a href="#">1805490000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 ST	
Type	BZT 1 ZA WS 10/5	Version
Order No.	<a href="#">1805520000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270248	
Qty.	100 ST	