

## CLI C 1-18 SDR SG

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

Version	CableLine, Conductor and cable markers, 2.5 - 5 mm, 18 x 4.2 mm, To customer specification
Order No.	<a href="#">1871809999</a>
Type	CLI C 1-18 SDR SG
GTIN (EAN)	4032248492893
Qty.	100 items
Delivery status	Discontinued
Available until	2025-12-10T00:00:00+01:00

**CLI C 1-18 SDR SG**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	5 mm	Depth (inches)	0.1968 inch
Height	18 mm	Height (inches)	0.7087 inch
Width	4.2 mm	Width (inches)	0.1654 inch
Net weight	0.23 g		

**Temperatures**

Operating temperature range -30...80 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Orientation of print	horizontal	Type of printing	To customer specification
Printing method	Ink jet technology	Version	Loop
Width	4.2 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Colour	To customer specification	Halogen	Yes
Basic material	PVC, soft, without Cadmium	Colour of printing	black
Printed characters	To customer specification	Operating temperature range	-30...80 °C
Imprint	Custom printing		

**Conductor and cable markers**

Halogen	Yes	Conductor cross-section, max.	4 mm <sup>2</sup>
Conductor cross-section, min.	1.5 mm <sup>2</sup>	Conductor O.D., max.	5 mm
Conductor O.D., min.	2.5 mm	Conductor O.D.	2.5 - 5 mm
Cross-section for connected wire	1.5 - 4 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**



Similar to illustration