

CLI C 2-6 GE/SW L2 CD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Version	CableLine, Conductor and cable markers, 4 - 10 mm, 6 x 7 mm, yellow
Order No.	1871901729
Type	CLI C 2-6 GE/SW L2 CD
GTIN (EAN)	4032248453276
Qty.	125 items

CLI C 2-6 GE/SW L2 CD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	8 mm	Depth (inches)	0.315 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	7 mm	Width (inches)	0.2756 inch
Net weight	0.37 g		

Temperatures

Operating temperature range -30...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Material colour according to resistance code	4		
Orientation of print	horizontal		
Type of printing	Standard		
Printing method	hot-embossing		
Version	CD		
Width	7 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-30 °C		
Colour	yellow		
Halogen	Yes		
Insulation cross-section, max.	10		
Basic material	PVC, soft, without Cadmium		
Colour of printing	black		
Printed characters	Mixed characters		
Number of markers per packaging unit	Form of supply	Reel	
Number of markers per combination	1 Reel = Conductor and cable markers		
Operating temperature range	-30...80 °C		
Imprint	L2		

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	2.5 mm ²	Conductor O.D., max.	10 mm
Conductor O.D., min.	4 mm	Conductor O.D.	4 - 10 mm
Cross-section for connected wire	2.5 - 16 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings



Similar to illustration