



Similar to illustration

Our extensive range of TM sleeves is suitable for all-purpose use. They cover a wide range of applications: from thin conductors to cables with large external diameters. This range offers printed inlay tags with maximum protection against outside influences. TM sleeves permit flexible installation.

- Optimum protection for printed inlay tags
- Wide range of applications for conductors and cables
- One tag type for all cross-sections
- TMX 30 for mounting with cable ties (width 4.6 mm)

#### General ordering data

|            |  |
|------------|--|
| Version    | TM, Socket x 9 mm, PVC, Colour: Transparent, Conductor O.D.: 6 - 10 mm |
| Order No.  | <a href="#">1874780000</a>   |
| Type       | TM 204/30 V0   |
| GTIN (EAN) | 4032248464562  |
| Qty.       | 200 items  |

Technical data

Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 30 mm  | Height (inches) | 1.1811 inch |
| Width      | 9 mm   | Width (inches)  | 0.3543 inch |
| Net weight | 1.38 g |                 |             |

Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -40...80 °C |
|-----------------------------|-------------|

Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

General data

|                                   |             |                                   |                           |
|-----------------------------------|-------------|-----------------------------------|---------------------------|
| Type of printing                  | neutral     | Width                             | 9 mm                      |
| UL 94 flammability rating         | V-0         | Operating temperature range, max. | 80 °C                     |
| Operating temperature range, min. | -40 °C      | Colour                            | Transparent               |
| Basic material                    | PVC         | Recommended industries            | Transportation, Machinery |
| Operating temperature range       | -40...80 °C |                                   |                           |

Conductor and cable markers

|                               |                    |                                  |                        |
|-------------------------------|--------------------|----------------------------------|------------------------|
| Conductor cross-section, max. | 16 mm <sup>2</sup> | Conductor cross-section, min.    | 6 mm <sup>2</sup>      |
| Conductor O.D., max.          | 10 mm              | Conductor O.D., min.             | 6 mm                   |
| Conductor O.D.                | 6 - 10 mm          | Cross-section for connected wire | 6 - 16 mm <sup>2</sup> |

Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |