

## CLI C 1-21 SDR SG


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

|            |  |
|------------|--|
| Version    | CableLine, Conductor and cable markers, 2.5 - 5 mm, 21 x 4.2 mm, To customer specification |
| Order No.  | <a href="#">1873370000</a>   |
| Type       | CLI C 1-21 SDR SG  |
| GTIN (EAN) | 4032248457465  |
| Qty.       | 100 items  |

**CLI C 1-21 SDR SG**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 5 mm   | Depth (inches)  | 0.1968 inch |
| Height     | 21 mm  | Height (inches) | 0.8268 inch |
| Width      | 4.2 mm | Width (inches)  | 0.1654 inch |
| Net weight | 0.01 g |                 |             |

**Temperatures**

Operating temperature range -30...60 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

|                                   |                            |                                   |                           |
|-----------------------------------|----------------------------|-----------------------------------|---------------------------|
| Orientation of print              | horizontal                 | Type of printing                  | To customer specification |
| Printing method                   | Ink jet technology         | Version                           | Loop                      |
| Width                             | 4.2 mm                     | UL 94 flammability rating         | V-0                       |
| Operating temperature range, max. | 60 °C                      | Operating temperature range, min. | -30 °C                    |
| Colour                            | To customer specification  | Halogen                           | Yes                       |
| Basic material                    | PVC, soft, without Cadmium | Colour of printing                | black                     |
| Printed characters                | To customer specification  | Operating temperature range       | -30...60 °C               |
| Imprint                           | Custom printing            |                                   |                           |

**Conductor and cable markers**

|                                  |                         |                               |                   |
|----------------------------------|-------------------------|-------------------------------|-------------------|
| Halogen                          | Yes                     | Conductor cross-section, max. | 4 mm <sup>2</sup> |
| Conductor cross-section, min.    | 1.5 mm <sup>2</sup>     | Conductor O.D., max.          | 5 mm              |
| Conductor O.D., min.             | 2.5 mm                  | Conductor O.D.                | 2.5 - 5 mm        |
| Cross-section for connected wire | 1.5 - 4 mm <sup>2</sup> |                               |                   |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**



Similar to illustration