


SM 22/22 K MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	SwitchMark, Device markers, 22 x 22 mm, To customer specification
Order No.	1877580000
Type	SM 22/22 K MC SDR
GTIN (EAN)	4032248467853
Qty.	16 items

SM 22/22 K MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	22 mm	Height (inches)	0.8661 inch
Width	22 mm	Width (inches)	0.8661 inch
Net weight	1.25 g		

Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.014 kg CO2 eq.

General data

Adhesive	Double-sided adhesive tape	
Printing method	MC Laser	
Version	Self-adhesive	
Width	22 mm	
UL 94 flammability rating	V-2	
Operating temperature range, max.	60 °C	
Operating temperature range, min.	-40 °C	
Colour	To customer specification	
Halogen	No	
Basic material	Polyamide 66	
Colour of printing	black	
Printed characters	Requires M-Print PRO File	
Number of markers per packaging unit	Form of supply	MultiCard
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2	
Number of markers per combination	1 MultiCard = Device markers	
Operating temperature range	-40...60 °C	

Device markers

Halogen	No
---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

SM 22/22 K MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Complementary products



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ETO SM 22/22 TRANSPAR.	Version	
Order No.	1880720000		SwitchMark, Protective cap, 22 x 22 mm, Transparent
GTIN (EAN)	4032248480883		
Qty.	10 ST		