

MFF 9/4 MC NE WS


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



MultiFit is the Weidmüller marker system used for other makes of terminals. Similar to the Weidmüller Dekafix, the markers of the MultiFit family are available ready-for-use with standard printing.

We recommend to carry out a test with sample markers on the terminals used when using MultiFit for the first time.

- One marker, suitable for different makes of terminals.
- Ready-to-use markers with standard printing
- Blank markers for printing with the PrintJet CONNECT or Plotter
- Delivery of individually printed markers according to customer CAE data or specifications
- One marking system for all applications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|------------|---|
| Version | MultiFit, Terminal marker, 9 x 4 mm, Pitch in mm (P): 4.00 Festo, white |
| Order No. | 1877720000 |
| Type | MFF 9/4 MC NE WS |
| GTIN (EAN) | 4032248468317 |
| Qty. | 500 items |

MFF 9/4 MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Height | 9 mm | Height (inches) | 0.3543 inch |
| Width | 4 mm | Width (inches) | 0.1575 inch |
| Net weight | 0.13 g | | |

Temperatures

Operating temperature range -40...100 °C

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.001 kg CO2 eq. | |

General data

| | | | |
|---|---|-----------|--|
| Material colour according to resistance code | 9 | | |
| Type of printing | neutral | | |
| Width | 4 mm | | |
| UL 94 flammability rating | V-2 | | |
| Operating temperature range, max. | 100 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | white | | |
| Halogen | No | | |
| Basic material | Polyamide 66 | | |
| Printed characters | neutral | | |
| Number of markers per packaging unit compatible printer | Form of supply | MultiCard | |
| | PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2 | | |
| Number of markers per combination | 1 MultiCard = Terminal marker | | |
| Operating temperature range | -40...100 °C | | |
| Application/manufacturer | Festo | | |

Connector markers

Pitch in mm (P) 4.00 mm

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000761 | ETIM 9.0 | EC000761 |
| ETIM 10.0 | EC000761 | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 | | |

Drawings



Drawing

