


**WFF 300/AH O.PS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

**General ordering data**

Version	Bolt-type screw terminals, Feed-through terminal, Rated cross-section: 300 mm <sup>2</sup> , Threaded stud connection
Order No.	<a href="#">1878650000</a>
Type	WFF 300/AH O.PS
GTIN (EAN)	4032248481194
Qty.	6 items

## WFF 300/AH O.PS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (UR)	E60693
Certificate No. (cURusEX)	E184763

## Dimensions and weights

Depth	85.5 mm	Depth (inches)	3.3661 inch
Depth including DIN rail	94 mm	Height	163 mm
Height (inches)	6.4173 inch	Width	55 mm
Width (inches)	2.1654 inch	Net weight	559.68 g

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

## System specifications

End cover plate required	No	Number of potentials	1
Number of levels	1	Number of clamping points per level	2
Levels cross-connected internally	No	PE connection	No
Mounting rail	TS 35	N-function	No
PE function	No	PEN function	No

## Additional technical data

Open sides	closed	Snap-on	Yes
Explosion-tested version	Yes	Type of mounting	TS 35

## Conductors for clamping (rated connection)

Cable lug to DIN 46234	25...240 mm <sup>2</sup>	Cable lug to DIN 46235	50...300 mm <sup>2</sup>
Connection direction	on side	Tightening torque, max.	60 Nm
Tightening torque, min.	25 Nm	Type of connection	Threaded stud connection
Number of connections	2	Clamping range, max.	300 mm <sup>2</sup>
Clamping range, min.	25 mm <sup>2</sup>	Wire connection cross section AWG, min.	AWG 4
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	25 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	25 mm <sup>2</sup>

## WFF 300/AH O.PS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

Wire connection cross section, finely stranded, max.	240 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	25 mm <sup>2</sup>
Connection cross-section, stranded, max.	300 mm <sup>2</sup>	Connection cross-section, stranded, min.	25 mm <sup>2</sup>
Stud size for spade connection	M 16	Wire connection cross-section, solid core, max.	240 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	25 mm <sup>2</sup>	Connection cross-section, finely stranded, min.	25 mm <sup>2</sup>
2 x cable lugs DIN 46 235	50...240 mm <sup>2</sup>	2 x cable lugs DIN 46 234	25 to 240 mm <sup>2</sup>

### General

Wire connection cross section AWG, min.	AWG 4	Standards	IEC 60947-7-1
Mounting rail	TS 35		

### Rating data

Rated cross-section	300 mm <sup>2</sup>	Rated voltage	1000 V
Rated DC voltage	1500 V	Nominal current	520 A
Current at maximum wires	520 A	Standards	IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	0.06 mΩ	Rated impulse withstand voltage	8 kV
Power loss in accordance with IEC 60947-7-x	16.64 W	Surge voltage category	III
Pollution severity	3		

### UL rating data

Conductor size Factory wiring max. (UR)	600 kcmil	Current size C (UR)	500 A
Voltage size C (UR)	1000 V	Conductor size Factory wiring min. (UR)	6 AWG
Certificate No. (UR)	E60693	Conductor size Field wiring min. (UR)	6 AWG
Conductor size Field wiring max. (UR)	600 kcmil		

### Important note

Product information	Cover without testhole
---------------------	------------------------

### Classifications

ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 14.0	27-25-01-01
ECLASS 15.0	27-25-01-01		

**Drawings**

