

HDC-KIT-HA 16.120**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The RockStar® kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard plug-in connector combinations with metric or PG cable entry threads, with screw connection or PUSH IN connection.

General ordering data

Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HA, Installation size: 5, Poles: 16, Screw connection, 250 V, 16 A, diecast aluminium, PG 16
Order No.	1884300000
Type	HDC-KIT-HA 16.120
GTIN (EAN)	4032248488582
Qty.	1 items

HDC-KIT-HA 16.120

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 430 g

Temperatures

Limit temperature -40 °C ... 100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3

SCIP bfb1c983-6f18-4ba4-8907-38aad6aee076

General data

Surface finish	Powder coating	Protection degree	IP65
Series	HA		

Version

Number of cable glands	1	Size of cable entries	PG 16
Top part/bottom part/lid	upper part, lower part	Number of cable entry sideways	1
Type of connection	Screw connection	Design of locking system	End-locking clamp, lower side
Installation size	5	Clamp version	End-locking clamp
Sealing	NBR	Colour (RAL)	RAL 7035
BG	5		

General data

Number of poles	16	Connection type PE	Screw connection
Installation size	5	Cable gland	PG 16
Basic material	diecast aluminium	Series	HA
Rated voltage (DIN EN 61984)	250 V	Rated current (DIN EN 61984)	16 A
BG	5		

Version

Blade size, slotted (screw connection)	SD 0.6 x 3.5	Wire connection cross section AWG, max.	AWG 14
Type of connection	Screw connection	Installation size	5
Volume resistance	≤2 mΩ	Wire connection cross section AWG, min.	AWG 20
Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Surface finish	Powder coating	Max. torque for main contact	0.55 Nm
Basic material	diecast aluminium	Min. torque for main contact	0.5 Nm
BG	5		

HDC-KIT-HA 16.120

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

HDC-KIT-HA 16.120

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

HDC COS

Various accessories are available for our inserts. This includes coding elements for the inserts.



General ordering data

Type	HDC COS 16	Version
Order No.	1431000000	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190052706	
Qty.	1 ST	
Type	HDC COS 24	Version
Order No.	1430900000	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190077228	
Qty.	1 ST	
Type	HDC COS 32	Version
Order No.	1430800000	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190176181	
Qty.	1 ST	

SPB

Various accessories are available for our inserts. This includes coding elements for the inserts.



General ordering data

Type	SPB-M 3	Version
Order No.	1203600000	Heavy-duty connectors, Accessories, Lock bolts
GTIN (EAN)	4008190120047	
Qty.	100 ST	