

## VT SFX 14/23 MC SDR V0


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



SlimFix X are halogen-free conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. SlimFix is an acknowledged and approved marker type in traffic engineering. The SF tool allows easy installation even in case of small markers.

- Halogen-free material
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |  |
|------------|--|
| Version    | SlimFix X, Conductor and cable markers, 7 - 40 mm, 23 x 14 mm, To customer specification |
| Order No.  | <a href="#">188960000</a>  |
| Type       | VT SFX 14/23 MC SDR V0   |
| GTIN (EAN) | 4032248496457  |
| Qty.       | 32 items   |

## VT SFX 14/23 MC SDR V0

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 0.8 mm | Depth (inches)  | 0.0315 inch |
| Height     | 23 mm  | Height (inches) | 0.9055 inch |
| Width      | 14 mm  | Width (inches)  | 0.5512 inch |
| Net weight | 0.5 g  |                 |             |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -50...120 °C |
|-----------------------------|--------------|

## Environmental Product Compliance

|                          |                             |                  |
|--------------------------|-----------------------------|------------------|
| RoHS Compliance Status   | Compliant without exemption |                  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                  |
| Product Carbon Footprint | Cradle to gate              | 0.006 kg CO2 eq. |

## General data

|                                      |   |           |
|--------------------------------------|---|-----------|
| Type of printing                     | To customer specification   |           |
| Printing method                      | MC Laser  |           |
| Version                              | Installation with cable ties  |           |
| Width                                | 14 mm   |           |
| UL 94 flammability rating            | V-0   |           |
| Operating temperature range, max.    | 120 °C  |           |
| Operating temperature range, min.    | -50 °C  |           |
| Colour                               | To customer specification   |           |
| Halogen                              | No  |           |
| Basic material                       | Polyamide 66  |           |
| Colour of printing                   | black   |           |
| Printed characters                   | Requires M-Print PRO File   |           |
| Advice label                         | Colour based on customer requirements (Please send M-Print PRO file)                        |           |
| Number of markers per packaging unit | Form of supply  | MultiCard |
| Size of labelling field              | 23 x 8 mm   |           |
| compatible printer                   | <a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a> |           |
| Number of markers per combination    | 1 MultiCard = Conductor and cable markers   |           |
| Operating temperature range          | -50...120 °C  |           |

## Conductor and cable markers

|                                  |                          |                               |                     |
|----------------------------------|--------------------------|-------------------------------|---------------------|
| Halogen                          | No                       | Conductor cross-section, max. | 500 mm <sup>2</sup> |
| Conductor cross-section, min.    | 16 mm <sup>2</sup>       | Conductor O.D., max.          | 40 mm               |
| Conductor O.D., min.             | 7 mm                     | Conductor O.D.                | 7 - 40 mm           |
| Cross-section for connected wire | 16 - 500 mm <sup>2</sup> |                               |                     |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |