

ESG 8/17 L MC NE WS


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ESG, Device markers x 17 mm, PA 66, Colour: white, pluggable
Order No.	1890470000
Type	ESG 8/17 L MC NE WS
GTIN (EAN)	4032248499335
Qty.	200 items

ESG 8/17 L MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.0315 inch
Height	8 mm	Height (inches)	0.315 inch
Width	17 mm	Width (inches)	0.6693 inch
Net weight	0.46 g		

Temperatures

Operating temperature range -40...100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.003 kg CO2 eq.	

General data

Material colour according to resistance code	9		
Version	pluggable		
Width	17 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	No		
Basic material	PA 66		
Printed characters	without		
Number of markers per packaging unit	Form of supply	MultiCard	
compatible printer	PRINTJET CONNECT, MCP BASIC 2, MCP PLUS 2		
Number of markers per combination	1 MultiCard = Device markers		
Operating temperature range	-40...100 °C		
Application/manufacturer	Lumberg		

Device markers

Halogen No

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

