


**WTD 6/4 FF**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image****Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

**General ordering data**

Version	Feed-through terminal block, Screw connection, dark beige, 6 mm <sup>2</sup> , 41 A, 800 V, Number of connections: 2
Order No.	<a href="#">1887220000</a>
Type	WTD 6/4 FF
GTIN (EAN)	4032248526802
Qty.	50 items

## WTD 6/4 FF

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

## Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURus)	E60693

## Dimensions and weights

Depth	52 mm	Depth (inches)	2.0472 inch
Depth including DIN rail	53.4 mm	Height	76.5 mm
Height (inches)	3.0118 inch	Width	11 mm
Width (inches)	0.4331 inch	Net weight	31.59 g

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...75 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

## System specifications

Version	Screw connection, for plug-in cross-connector, One end without connector	End cover plate required	Yes
Number of potentials	1	Number of levels	1
Number of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Mounting rail	TS 35, TS 32	N-function	No
PE function	No	PEN function	No

## Additional technical data

Explosion-tested version	No	Type of mounting	Snap-on
--------------------------	----	------------------	---------

## CSA rating data

Voltage size B (cCSAus)	600 V	Voltage size C (cCSAus)	600 V
Current size D (cCSAus)	40 A	Wire cross section min. (cCSAusX)	26 AWG
Current size C (cCSAus)	40 A	Certificate number (cCSAus)	227775-1609344
Wire cross section max. (cCSAusX)	10 AWG	Current size B (cCSAus)	40 A
Voltage size D (cCSAus)	600 V		

## WTD 6/4 FF

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Conductors for clamping (additional connection)

Connection type, additional connection Screw connection

## Conductors for clamping (rated connection)

Wire connection cross section AWG, max.	AWG 10	Connection direction	on side
Tightening torque, max.	2.4 Nm	Tightening torque, min.	1.2 Nm
Stripping length	8 mm	Type of connection	Screw connection
Number of connections	2	Clamping range, max.	6 mm <sup>2</sup>
Clamping range, min.	1.5 mm <sup>2</sup>	Clamping screw	M 4
Blade size	0.8 x 5.5 mm	Wire connection cross section AWG, min.	AWG 16
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	6 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	1.5 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	6 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	1.5 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	6 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	1.5 mm <sup>2</sup>
Connection cross-section, stranded, max.	6 mm <sup>2</sup>	Connection cross-section, stranded, min. 1.5 mm <sup>2</sup>	
Wire connection cross-section, solid core, max.	10 mm <sup>2</sup>	Wire connection cross-section, solid core, min.	1.5 mm <sup>2</sup>
Connection cross-section, finely stranded, min.	1.5 mm <sup>2</sup>		

## Dimensions

TS 32 offset 38.5 mm TS 35 offset 38.5 mm

## General

Wire connection cross section AWG, max.	AWG 10	Wire connection cross section AWG, min.	AWG 16
Standards	IEC 60947-7-1	Mounting rail	TS 35, TS 32

## Rating data

Rated cross-section	6 mm <sup>2</sup>	Rated voltage	800 V
Rated DC voltage	800 V	Nominal current	41 A
Current at maximum wires	41 A	Standards	IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	0.78 mΩ	Rated impulse withstand voltage	8 kV
Power loss in accordance with IEC 60947-7-x	1.31 W	Pollution severity	3

## UL rating data

Conductor size Factory wiring max. (cURus)	10 AWG	Voltage size B (cURus)	600 V
Certificate No. (cURus)	E60693	Conductor size Field wiring min. (cURus)	26 AWG
Conductor size Factory wiring min. (cURus)	26 AWG	Current size B (cURus)	30 A
Voltage size C (cURus)	600 V	Current size C (cURus)	30 A
Conductor size Field wiring max. (cURus)	10 AWG		

**WTD 6/4 FF**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Classifications**


ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 14.0	27-25-01-01
ECLASS 15.0	27-25-01-01		

**WTD 6/4 FF**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)



## WTD 6/4 FF

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

Type	ZQV 10/2	Version
Order No.	<a href="#">1739680000</a>	Accessories, Cross-connector, 57 A
GTIN (EAN)	4008190957131	
Qty.	25 ST	
Type	Q 2 WTL6/4FF	Version
Order No.	<a href="#">1897110000</a>	Cross-connector (terminal), when screwed in, Silver grey, 41 A,
GTIN (EAN)	4032248514083	Number of poles: 2, Pitch in mm (P): 11.00, Insulated: No, Width: 2
Qty.	100 ST	mm
Type	Q 4 WTL 6/4FF	Version
Order No.	<a href="#">1897130000</a>	Cross-connector (terminal), when screwed in, Silver grey, 41 A,
GTIN (EAN)	4032248514106	Number of poles: 4, Pitch in mm (P): 11.00, Insulated: No, Width: 2
Qty.	100 ST	mm

## Accessorie



Current and voltage transformer wiring  
Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

## General ordering data

Type	Q 10 WTL 6/4FF	Version
Order No.	<a href="#">1897190000</a>	Cross-connector (terminal), when screwed in, Silver grey, 41 A,
GTIN (EAN)	4032248514168	Number of poles: 10, Pitch in mm (P): 11.00, Insulated: No, Width: 2
Qty.	50 ST	mm
Type	QL 2 WTL6/4FF	Version
Order No.	<a href="#">1897010000</a>	Cross-connector (terminal), when screwed in, Silver grey, 41 A,
GTIN (EAN)	4032248513987	Number of poles: 2, Pitch in mm (P): 11.00, Insulated: No, Width: 2
Qty.	100 ST	mm
Type	QL 3 WTL6/4FF	Version
Order No.	<a href="#">1897020000</a>	Cross-connector (terminal), when screwed in, Silver grey, 41 A,
GTIN (EAN)	4032248513994	Number of poles: 3, Pitch in mm (P): 11.00, Insulated: No, Width: 2
Qty.	100 ST	mm

## WTD 6/4 FF

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

Type	QL 4 WTL6/4FF	Version
Order No.	<a href="#">1897030000</a>	Cross-connector (terminal), when screwed in, Silver grey, 41 A,
GTIN (EAN)	4032248514007	Number of poles: 4, Pitch in mm (P): 11.00, Insulated: No, Width: 2
Qty.	100 ST	mm
Type	QL 10 WTL 6/4 FF	Version
Order No.	<a href="#">1897090000</a>	Cross-connector (terminal), when screwed in, Silver grey, 41 A,
GTIN (EAN)	4032248514069	Number of poles: 10, Pitch in mm (P): 11.00, Insulated: No, Width: 2
Qty.	100 ST	mm

## End plates and partition plates




Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

## General ordering data

Type	WAP WTL6/4FF	Version
Order No.	<a href="#">1887240000</a>	End plate for terminals, dark beige, Height: 68.5 mm, Width: 1.5 mm,
GTIN (EAN)	4032248526819	V-0, Wemid, Snap-on: No
Qty.	20 ST	

## End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## WTD 6/4 FF

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## General ordering data

Type	WEW 35/2	Version
Order No.	<a href="#">1061200000</a>	End bracket, dark beige, TS 35, HB, Wemid, Width: 8 mm, 100 °C
GTIN (EAN)	4008190030230	
Qty.	50 ST	

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

Type	VH 13.5/4.9/3.3	Version
Order No.	<a href="#">0248500000</a>	Connecting sleeve (terminal), when screwed in, Width: 4.9 mm,
GTIN (EAN)	4008190022723	Height: 4.9 mm, Depth: 13.5 mm, Number of poles: 1, Copper
Qty.	100 ST	
Type	KISC M3X20.5/10 EK4	Version
Order No.	<a href="#">0303000000</a>	Clamping yoke, Mounting screw, Steel
GTIN (EAN)	4008190163686	
Qty.	100 ST	

## Disconnect plugs



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

## General ordering data

Type	QS 2/12/4	Version
Order No.	<a href="#">0270760000</a>	Cross-connector (terminal), Plugged, beige, 44 A, Number of poles: 2,
GTIN (EAN)	4008190011420	Pitch in mm (P): 12.00, Insulated: Yes, Width: 12 mm
Qty.	20 ST	

## WTD 6/4 FF

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Ring cable lugs




Insulated ring-cable connector made from PVC

- Commercially available designs
- Not soldered
- With conical entry funnel

## General ordering data

Type	LIR 1,5M4 V	Version
Order No.	<a href="#">9200090000</a>	cable lug, terminal end,Insulated cable connector,1.5 mm <sup>2</sup> ,0.5 mm <sup>2</sup> -
GTIN (EAN)	4032248409853	1.5 mm <sup>2</sup>
Qty.	100 ST	
Type	LIR 2,5M4 V	Version
Order No.	<a href="#">9200170000</a>	cable lug, terminal end,Insulated cable connector,2.5 mm <sup>2</sup> ,1.5 mm <sup>2</sup> -
GTIN (EAN)	4032248409792	2.5 mm <sup>2</sup>
Qty.	100 ST	
Type	LIR 6M4 V	Version
Order No.	<a href="#">9200230000</a>	cable lug, terminal end,Insulated cable connector,6 mm <sup>2</sup> ,4 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4032248410057	
Qty.	100 ST	

## Slotted screwdriver



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

## General ordering data

Type	SDIS 0.6X3.5X100	Version
Order No.	<a href="#">9008390000</a>	Screwdriver, Screwdriver
GTIN (EAN)	4032248056354	
Qty.	1 ST	

## WTD 6/4 FF

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Crimping tools



Crimping tools for insulated connectors  
cable lugs, terminal pins, parallel and serial connectors,  
plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

## General ordering data

Type	CTI 6	Version
Order No.	<a href="#">9006120000</a>	Pressing tool, Crimping tool for contacts, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> , Oval
GTIN (EAN)	4008190044527	crimping, Double crimp
Qty.	1 ST	

## Testadapter and testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

Type	PS 4 F.STB 4	Version
Order No.	<a href="#">0299600000</a>	Test adapter (terminal), 230 V
GTIN (EAN)	4008190074043	
Qty.	20 ST	

## Accessorie



Current and voltage transformer wiring  
Our test disconnect terminal blocks featuring spring  
and screw connection technology allow you to create all  
the important converter circuits for measuring current,  
voltage and power in a safe and sophisticated way.

## General ordering data

Type	WQB 10 WTL 6/4 FF	Version
Order No.	<a href="#">2550780000</a>	Cross-connector (terminal), when screwed in, orange, 41 A, Number
GTIN (EAN)	4050118560640	of poles: 10, Pitch in mm (P): 11.10, Insulated: Yes, Width: 106.9 mm
Qty.	10 ST	

## WTD 6/4 FF

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

Type	WQB 12 WTL 6/4 FF	Version
Order No.	<a href="#">2552080000</a>	Cross-connector (terminal), when screwed in, orange, 41 A, Number
GTIN (EAN)	4050118577655	of poles: 12, Pitch in mm (P): 11.10, Insulated: Yes, Width: 129.1 mm
Qty.	10 ST	

## Accessorie



Current and voltage transformer wiring  
Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

## General ordering data

Type	WQB 2 WTL 6/4 FF	Version
Order No.	<a href="#">2550640000</a>	Cross-connector (terminal), when screwed in, orange, 41 A, Number
GTIN (EAN)	4050118560503	of poles: 2, Pitch in mm (P): 11.10, Insulated: Yes, Width: 18.2 mm
Qty.	10 ST	
Type	WQB 3 WTL 6/4 FF	Version
Order No.	<a href="#">2550740000</a>	Cross-connector (terminal), when screwed in, orange, 41 A, Number
GTIN (EAN)	4050118560602	of poles: 3, Pitch in mm (P): 11.10, Insulated: Yes, Width: 29.3 mm
Qty.	10 ST	
Type	WQB 4 WTL 6/4 FF	Version
Order No.	<a href="#">2550750000</a>	Cross-connector (terminal), when screwed in, orange, 41 A, Number
GTIN (EAN)	4050118560619	of poles: 4, Pitch in mm (P): 11.10, Insulated: Yes, Width: 40.4 mm
Qty.	10 ST	

## WTD 6/4 FF

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

Type	WQB 5 WTL 6/4 FF	Version
Order No.	<a href="#">2550760000</a>	Cross-connector (terminal), when screwed in, orange, 41 A, Number
GTIN (EAN)	4050118560626	of poles: 5, Pitch in mm (P): 11.10, Insulated: Yes, Width: 51.5 mm
Qty.	10 ST	

## Accessorie



Current and voltage transformer wiring  
Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

## General ordering data

Type	WQB 6 WTL 6/4 FF	Version
Order No.	<a href="#">2551490000</a>	Cross-connector (terminal), when screwed in, orange, 41 A, Number
GTIN (EAN)	4050118577648	of poles: 6, Pitch in mm (P): 11.10, Insulated: Yes, Width: 62.6 mm
Qty.	10 ST	
Type	WQB 7 WTL 6/4 FF	Version
Order No.	<a href="#">2550770000</a>	Cross-connector (terminal), when screwed in, orange, 41 A, Number
GTIN (EAN)	4050118560633	of poles: 7, Pitch in mm (P): 11.10, Insulated: Yes, Width: 73.7 mm
Qty.	10 ST	


## WTD 6/4 FF

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text.

WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	WS 12/9.5-11 MC NE WS	Version
Order No.	<a href="#">2484220000</a>	, Polyamide 66, Colour: white
GTIN (EAN)	4050118494808	
Qty.	300 ST	

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

Type	BZT 1 WS 10/5	Version
Order No.	<a href="#">1805490000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 ST	
Type	BZT 1 ZA WS 10/5	Version
Order No.	<a href="#">1805520000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270248	
Qty.	100 ST	