

SAIL-VSA-1.5U-230**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller can supply valve plugs as connecting lines with M8/M12 plugs and one end without connector. The status of the valve plug is shown by an LED. The valve plugs have a protective circuit. The Weidmüller range includes valve plugs of type A, B and C to DIN and industry standards. Protection class IP 67 is fulfilled when screwed in. The outlet direction is also a decisive factor, therefore Weidmüller offers different versions.

General ordering data

Version	Valve cable (assembled), 90° plug - valve plug, Design A (18 mm), Cable length: 1.5 m, PUR, black
Order No.	1891000150
Type	SAIL-VSA-1.5U-230
GTIN (EAN)	4099986010437
Qty.	1 items

SAIL-VSA-1.5U-230

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals	CE; UKCA
ROHS	Conform

Dimensions and weights

Net weight	76 g
------------	------

Technical specifications for cable

Cable length	1.5 m	Sheathing colour	black
PE function	Yes	Suitable for cable carriers	Yes
Core cross-section	0.5 mm ²	Shielded	No
Halogen	No	Insulation	PP
Bending radius, min., moving	10 x cable diameter	Bending radius, min., stationary	5 x cable diameter
Sheath material	PUR	Configurable cable length	No
Irradiation crosslinked	No	Temperature range, stationary	-50...80 °C
Temperature range, moving	-25...80 °C	Number of poles	3 (2 + PE)
Outside diameter	4.6 mm ± 0.2 mm		

General technical data

Coding	Design A (18 mm)	Connection thread	Miscellaneous
Contact surface	tinned	LED	Yes
Version	90° plug - valve plug	Contact material	CuZn
Nominal voltage	230 V	Nominal current	4 A
Protection degree	IP67, IP65 in acc. with DIN EN 60529	Temperature range of housing	-25...+80 °C

Plug, left

Plug left	Valve plug, Design A (18 mm), Number of poles: 4, female contact, angled 0°, plug, LED yellow, unshielded
-----------	---

Plug, right


Plug right	Free conductor end
------------	--------------------

Classifications


ETIM 8.0	EC001855	ETIM 9.0	EC001855
ETIM 10.0	EC001855	ECLASS 14.0	27-06-03-12
ECLASS 15.0	27-06-03-12		

Drawings

Dimensioned drawing



Pole scheme



Wiring diagram

