

**TM 0/18 TWIN HF/HB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

TM/HF Twin double-sided labelling: 0.22 – 2.5 mm<sup>2</sup>.

Twin sleeves enable double-sided marking of a conductor. The sleeves can hold two TM-I 18 tags so that, for example, the input and output designations of a cable can be read at one position. The transparent, halogen-free sleeves can be used on conductors with an outside diameter of 1.3 to 4.0 mm.

**General ordering data**

Version	TM, Socket x 5 mm, Polyethylene LD, Colour: Transparent, Conductor O.D.: 1.3 - 2.6 mm
Order No.	<a href="#">1891810000</a>
Type	TM 0/18 TWIN HF/HB
GTIN (EAN)	4032248504558
Qty.	500 items

TM 0/18 TWIN HF/HB

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	10	Depth (inches)	0.3937 inch
Height	18 mm	Height (inches)	0.7087 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	0.23 g		

Temperatures

Operating temperature range -40...80 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.001 kg CO2 eq.	

General data

Type of printing	neutral	Width	5 mm
UL 94 flammability rating	HB	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Colour	Transparent
Halogen	No	Basic material	Polyethylene LD
Recommended industries	Transportation, Machinery	Operating temperature range	-40...80 °C

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	1.5 mm <sup>2</sup>
Conductor cross-section, min.	0.22 mm <sup>2</sup>	Conductor O.D., max.	2.6 mm
Conductor O.D., min.	1.3 mm	Conductor O.D.	1.3 - 2.6 mm
Cross-section for connected wire	0.22 - 1.5 mm <sup>2</sup>		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		