

## MF-SI 10/6 MC SDR


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

MultiFit is the Weidmüller marker system used for other makes of terminals. Similar to the Weidmüller Dekafix, the markers of the MultiFit family are available ready-for-use with standard printing.

We recommend to carry out a test with sample markers on the terminals used when using MultiFit for the first time.

- One marker, suitable for different makes of terminals.
- Ready-to-use markers with standard printing
- Blank markers for printing with the PrintJet CONNECT or Plotter
- Delivery of individually printed markers according to customer CAE data or specifications
- One marking system for all applications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |  |
|------------|--|
| Version    | MultiFit, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Siemens, To customer specification |
| Order No.  | <a href="#">1889250000</a>   |
| Type       | MF-SI 10/6 MC SDR  |
| GTIN (EAN) | 4032248495559  |
| Qty.       | 64 items   |

**MF-SI 10/6 MC SDR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |       |                 |             |
|------------|-------|-----------------|-------------|
| Height     | 10 mm | Height (inches) | 0.3937 inch |
| Width      | 6 mm  | Width (inches)  | 0.2362 inch |
| Net weight | 0.2 g |                 |             |

**Temperatures**

Operating temperature range -40...100 °C

**Environmental Product Compliance**

|                          |                             |                  |  |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status   | Compliant without exemption |                  |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                  |  |
| Product Carbon Footprint | Cradle to gate              | 0.002 kg CO2 eq. |  |

**General data**

|                                      |                               |           |  |
|--------------------------------------|-------------------------------|-----------|--|
| Orientation of print                 | horizontal and vertical       |           |  |
| Printing method                      | MC Laser                      |           |  |
| Width                                | 6 mm                          |           |  |
| UL 94 flammability rating            | V-2                           |           |  |
| Operating temperature range, max.    | 100 °C                        |           |  |
| Operating temperature range, min.    | -40 °C                        |           |  |
| Colour                               | To customer specification     |           |  |
| Halogen                              | No                            |           |  |
| Basic material                       | Polyamide 66                  |           |  |
| Colour of printing                   | black                         |           |  |
| Printed characters                   | Requires M-Print PRO File     |           |  |
| Number of markers per packaging unit | Form of supply                | MultiCard |  |
| Number of markers per combination    | 1 MultiCard = Terminal marker |           |  |
| Operating temperature range          | -40...100 °C                  |           |  |
| Application/manufacturer             | Siemens                       |           |  |

**Connector markers**

Pitch in mm (P) 6.00 mm

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |

**Drawings**



**Drawing**