

**CLI T 2-30****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The CLI T sleeve is a high-quality, transparent sleeve for marking conductors and cables with cross-sections up to 75 mm<sup>2</sup>. The CLI T sleeve is available in four lengths so that labelling with long character strings is possible. The transparent sleeve optimally protects the inlay tag against outside influences. As inlay tag the TM-I marker from the MultiCard and MultiMark portfolio be suitable.

- Wider cross-section range per sleeve
- A special flexible bellow profile ensures a wide application range
- Easy insertion of the TM-I tag into the sleeve pocket before or after connecting the conductor
- Available in five lengths
- Not suitable for labelling with P-Ink or STI pen

**General ordering data**

|            |                                                                               |
|------------|-------------------------------------------------------------------------------|
| Version    | CableLine, Socket x 5 mm, PVC, Colour: Transparent, Conductor O.D.: 4 - 10 mm |
| Order No.  | <a href="#">1889570000</a>                                                    |
| Type       | CLI T 2-30                                                                    |
| GTIN (EAN) | 4032248496372                                                                 |
| Qty.       | 100 items                                                                     |

## CLI T 2-30

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |       |                 |             |
|------------|-------|-----------------|-------------|
| Height     | 30 mm | Height (inches) | 1.1811 inch |
| Width      | 5 mm  | Width (inches)  | 0.1968 inch |
| Net weight | 1 g   |                 |             |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General data

|                                   |             |                                   |                           |
|-----------------------------------|-------------|-----------------------------------|---------------------------|
| Type of printing                  | neutral     | Width                             | 5 mm                      |
| UL 94 flammability rating         | V-0         | Operating temperature range, max. | 80 °C                     |
| Operating temperature range, min. | -30 °C      | Colour                            | Transparent               |
| Halogen                           | Yes         | Basic material                    | PVC                       |
| Printed characters                | without     | Recommended industries            | Transportation, Machinery |
| Operating temperature range       | -30...80 °C | Number per roll                   | 100                       |

### Conductor and cable markers

|                                  |                        |                               |                    |
|----------------------------------|------------------------|-------------------------------|--------------------|
| Halogen                          | Yes                    | Conductor cross-section, max. | 35 mm <sup>2</sup> |
| Conductor cross-section, min.    | 4 mm <sup>2</sup>      | Conductor O.D., max.          | 10 mm              |
| Conductor O.D., min.             | 4 mm                   | Conductor O.D.                | 4 - 10 mm          |
| Cross-section for connected wire | 4 - 35 mm <sup>2</sup> |                               |                    |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |