


## MF-SI 10/5-6.5 MC SDR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration



MultiFit is the Weidmüller marker system used for other makes of terminals. Similar to the Weidmüller Dekafix, the markers of the MultiFit family are available ready-for-use with standard printing.

We recommend to carry out a test with sample markers on the terminals used when using MultiFit for the first time.

- One marker, suitable for different makes of terminals.
- Ready-to-use markers with standard printing
- Blank markers for printing with the PrintJet CONNECT or Plotter
- Delivery of individually printed markers according to customer CAE data or specifications
- One marking system for all applications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Version	MultiFit, Terminal marker, 10 x 5 mm, Pitch in mm (P): 6.50 Siemens, To customer specification
Order No.	<a href="#">1889790000</a>
Type	MF-SI 10/5-6.5 MC SDR
GTIN (EAN)	4032248497355
Qty.	64 items

## MF-SI 10/5-6.5 MC SDR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Height	10 mm	Height (inches)	0.3937 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	0.3 g		

### Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.002 kg CO2 eq.	

### General data


Orientation of print	horizontal and vertical		
Printing method	MC Laser		
Width	5 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	To customer specification		
Halogen	No		
Basic material	Polyamide 66		
Colour of printing	black		
Printed characters	Requires M-Print PRO File		
Number of markers per packaging unit	Form of supply	MultiCard	
Number of markers per combination	1 MultiCard = Terminal marker		
Operating temperature range	-40...100 °C		
Application/manufacturer	Siemens		

### Connector markers

Pitch in mm (P)	6.50 mm
-----------------	---------

### Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		



**Drawing**