

TM 1/18 TWIN HF/HB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

TM/HF Twin double-sided labelling: 0.22 – 2.5 mm².
Twin sleeves enable double-sided marking of a conductor. The sleeves can hold two TM-I 18 tags so that, for example, the input and output designations of a cable can be read at one position. The transparent, halogen-free sleeves can be used on conductors with an outside diameter of 1.3 to 4.0 mm.

General ordering data

Version	TM, Socket x 5 mm, Polyethylene LD, Colour: Transparent, Conductor O.D.: 2.4 - 4 mm
Order No.	1891780000
Type	TM 1/18 TWIN HF/HB
GTIN (EAN)	4032248504527
Qty.	500 items

TM 1/18 TWIN HF/HB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	12	Depth (inches)	0.4724 inch
Height	18 mm	Height (inches)	0.7087 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	0.28 g		

Temperatures

Operating temperature range -40...80 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.001 kg CO2 eq.	

General data

Type of printing	neutral	Width	5 mm
UL 94 flammability rating	HB	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Colour	Transparent
Halogen	No	Basic material	Polyethylene LD
Recommended industries	Transportation, Machinery	Operating temperature range	-40...80 °C

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	2.5 mm ²
Conductor cross-section, min.	1.5 mm ²	Conductor O.D., max.	4 mm
Conductor O.D., min.	2.4 mm	Conductor O.D.	2.4 - 4 mm
Cross-section for connected wire	1.5 - 2.5 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		