


SAIS-M23-12P-ST-5,0M

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

The M23 cables offer: high mating frequency, high current carrying capacity and high-density contacts coupled with minimal dimensions.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

Version	Sensor/actuator line, One end without connector, M23, External thread, Number of poles: 12, 5 m, pin, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
Order No.	1906280500
Type	SAIS-M23-12P-ST-5,0M
GTIN (EAN)	4032248528806
Qty.	1 items

SAIS-M23-12P-ST-5,0M

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E486077

Dimensions and weights

Net weight	431.2 g
------------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	e8d8af70-4c85-4483-bc8c-9bc5b598e2a9

Technical specifications for cable

Cable length	5 m	Sheathing colour	black
Suitable for cable carriers	Yes	Shielded	No
Halogen	No	Insulation	TPM
Bending radius, min., moving	10 x cable diameter	Bending cycles	2 Mio
Wire cross section (Print/Online)	3 x 0.75 mm ² + 8 x 0.34 mm ²	Sheath material	PUR
Outer cladding in accordance with UL AWM style	21198 (80 °C / 300 V)	Irradiation crosslinked	No
Welding spark resistance	No	Colour coding	white, green, yellow, grey, pink, red, black, violet, blue, brown, Green/yellow
Torsion resistance	0 °/m	Temperature range, stationary	-50...80 °C
Resistant to welding beads	No	Temperature range, moving	-25...80 °C
Number of poles	12	Outside diameter	7.7 mm ± 0.3 mm

General technical data

Connection thread	M23, External thread		
Contact surface	Gold-plated		
LED	No		
Version	pin, straight		
Housing main material	PUR		
Insulation resistance	1012 Ω		
Nominal voltage	120 V		
Nominal current	8 A		
Protection degree	IP67		
Plugging cycles	≥ 50		
Pollution severity	2		
jumpered	No		
Connection side version	Connection side	1	
	Connection thread	M23	
	Type of contact	Pin	
	Type of thread	External thread	
	Outlet direction	angled	
Connection side version 1	M23, Pin, External thread, angled		

SAIS-M23-12P-ST-5,0M

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Threaded ring material	Diecast zinc
Temperature range of housing	-25...+80 °C
Tightening torque	M23: 2.5 Nm

Electrical properties

Insulation resistance	1012 Ω	Nominal voltage	120 V
-----------------------	--------	-----------------	-------

General standards

Certificate No. (cURus)	E486077
-------------------------	---------

Plug, left

Plug left	IP67, male contact, straight, Plastic, unshielded
-----------	---

Plug, right

Plug right	free conductor end
------------	--------------------


Classifications

ETIM 8.0	EC001855	ETIM 9.0	EC001855
ETIM 10.0	EC001855	ECLASS 14.0	27-06-03-11
ECLASS 15.0	27-06-03-11		


SAIS-M23-12P-ST-5,0M

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings**Dimensioned drawing**

Male, straight

Pole scheme

Male

Wiring diagram**The ideal tool: Screwty ® with torque function**

Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F

SAIS-M23-12P-ST-5,0M

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

SAIS-M23-12P-ST-5,0M

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories**General ordering data**

Type	SCREWTY M23	Version
Order No.	1981560000	Cable gland tool adapter for M23 lines and connectors
GTIN (EAN)	4032248677702	
Qty.	1 ST	

Screwty® cable gland tool with torque function**General ordering data**

Type	1/4" HANDGRIFF	Version
Order No.	4294820000	Bolting tool
GTIN (EAN)	4032248478279	
Qty.	1 ST	