Data sheet

SAIS-M23-12P-AN-1,0M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com









Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.
The M23 cables offer: high mating frequency, high current carrying capacity and high-density contacts coupled with minimal dimensions.
Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

Version	Sensor/actuator line, One end without connector, M23, External thread, Number of poles: 12, 1 m, pin, 90°, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
Order No.	1906290100
Type	SAIS-M23-12P-AN-1,0M
GTIN (EAN)	4032248528837
Qty.	1 items

Data sheet

SAIS-M23-12P-AN-1,0M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E486077

Dimensions and weights

Net weight	170 g

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical specifications for cable

Cable length	1 m	Sheathing colour	black
Suitable for cable carriers	Yes	Shielded	No
Halogen	No	Insulation	TPM
Bending radius, min., moving	10 x cable diameter	Bending cycles	2 Mio
Wire cross section (Print/Online)	3 x 0.75 mm² + 8 x 0.34 mm²	Sheath material	PUR
Outer cladding in accordance with UL AWM style	21198 (80 °C / 300 V)	Irradiation crosslinked	No
Welding spark resistance	No	Colour coding	white, green, yellow, grey, pink, red, black, violet, blue, brown, Green/yellow
Torsion resistance	0 °/m	Temperature range, stationary	-50...80 °C
Resistant to welding beads	No	Temperature range, moving	-25...80 °C
Number of poles	12	Outside diameter	7.7 mm ± 0.3 mm

General technical data

Connection thread	M23, External thread	
Contact surface	Gold-plated	
LED	No	
Version	pin, 90°	
Housing main material	PUR	
Insulation resistance	1012 Ω	
Nominal voltage	120 V	
Nominal current	8 A	
Protection degree	IP67	
Plugging cycles	≥ 50	
Pollution severity	2	
jumpered	No	
Connection side version	Connection side	1
	Connection thread	M23
	Type of contact	Pin
	Type of thread	External thread
	Outlet direction	angled
Connection side version 1	M23, Pin, External thread, angled	

Data sheet

SAIS-M23-12P-AN-1,0M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Threaded ring material	Diecast zinc
Temperature range of housing	-25…+80 °C
Tightening torque	M23: 2.5 Nm

Electrical properties

Insulation resistance	1012 Ω	Nominal voltage	120 V

General standards

Certificate No. (cURus)	E486077

Plug, left

Plug left	IP67, male contact, angled 90°, Plastic, unshielded

Plug, right

Plug right	free conductor end

Classifications

ETIM 8.0	EC001855	ETIM 9.0	EC001855
ETIM 10.0	EC001855	ECLASS 14.0	27-06-03-11
ECLASS 15.0	27-06-03-11		


SAIS-M23-12P-AN-1,0M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com


Drawings

Dimensioned drawing




Male, angled

Pole scheme



Male

Wiring diagram



The ideal tool: Screwty ® with torque function

Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings