


**ZQV 4/20 GE****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Z-series, Cross-connector, For the terminals, Number of poles: 20
Order No.	<a href="#">1909010000</a>
Type	ZQV 4/20 GE
GTIN (EAN)	4032248535637
Qty.	20 items

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	31.6 mm	Depth (inches)	1.2441 inch
Height	120.3 mm	Height (inches)	4.7362 inch
Width	2.8 mm	Width (inches)	0.1102 inch
Net weight	18.2 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-60 °C...85 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

### System specifications

Version	For the terminals
---------	-------------------

### Additional technical data

Type of fixing	Plugged	Installation advice	Direct mounting
Explosion-tested version	No		

### Dimensions

Pitch in mm (P)	6.10 mm
-----------------	---------

### General

Number of poles	20	Installation advice	Direct mounting
-----------------	----	---------------------	-----------------

### Rating data

Rated voltage	400 V	Nominal current	32 A
---------------	-------	-----------------	------

### Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used Cross connections with >10 poles have bare cut edges ex works.
---------------------	---

## Technical data

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		