


## VT SF 00/21 MC SDR V0

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

#### Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

#### General ordering data

Version	SlimFix, Conductor and cable markers, 1 - 1.3 mm, 21 x 3.2 mm, To customer specification
Order No.	<a href="#">1906370000</a>
Type	VT SF 00/21 MC SDR V0
GTIN (EAN)	4032248528752
Qty.	80 items

## VT SF 00/21 MC SDR V0

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	3.2 mm	Depth (inches)	0.126 inch
Height	21 mm	Height (inches)	0.8268 inch
Width	3.2 mm	Width (inches)	0.126 inch
Net weight	0.23 g		

## Temperatures

Operating temperature range	-50...120 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
Product Carbon Footprint	Cradle to gate 0.003 kg CO2 eq.

## General data

Orientation of print	horizontal
Type of printing	To customer specification
Printing method	MC Laser
Width	3.2 mm
UL 94 flammability rating	V-0
Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C
Colour	To customer specification
Halogen	No
Basic material	Polyamide 66
Colour of printing	black
Printed characters	Requires M-Print PRO File
Advice label	Colour based on customer requirements (Please send M-Print PRO file)
Number of markers per packaging unit	Form of supply MultiCard
Size of labelling field	21 x 3.2 mm
compatible printer	<a href="#">PRINTJET CONNECT, MCP BASIC 2, MCP PLUS 2</a>
Number of markers per combination	1 MultiCard = Conductor and cable markers
Operating temperature range	-50...120 °C

## Conductor and cable markers

Halogen	No	Conductor cross-section, max.	0.25 mm <sup>2</sup>
Conductor cross-section, min.	0.25 mm <sup>2</sup>	Conductor O.D., max.	1.3 mm
Conductor O.D., min.	1 mm	Conductor O.D.	1 - 1.3 mm
Cross-section for connected wire	0.25 - 0.25 mm <sup>2</sup>		

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		