

VG M32 - MS 1/EMV

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

Produktabbildung

The increasing sensitivity of electronic components and the increasing electromagnetic interference frequencies require cable glands to play an important role in the shielding concept of a system. This type of EMC cable glands are made for shielding against interference frequencies, with a 360° screening connection. A Finger-locking seal provides superior cable retention & strain relief, next to it, the cable gland meets the mechanical requirements of EN 62444. Due to the patented design a very easy and fast assembly will be possible.

General ordering data

Version	VG EMV GEN 1 (EMC cable gland with clamping cage). Cable glands, straight, M 32, 8, OD min. 15 - OD max. 21 mm, IP68 - 5 bar (30 min.), IP69K, Brass, nickel-plated
Order No.	1909530000
Type	VG M32 - MS 1/EMV
GTIN (EAN)	4032248536450
Qty.	10 items

VG M32 - MS 1/EMV

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



RoHS Conform

Dimensions and weights

Height	38 mm	Height (inches)	1.4961 inch
Length	46 mm	Length (inches)	1.811 inch
Net weight	88 g		

Temperatures

Operating temperature -40 °C...100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

Certificate numbers cable gland

Certificate no. cable gland (GERMLLOYD)	E-14047	Certificate no. cable gland (UL)	E-199260
Certificate no. cable gland (cULus)	E-199260	Approval conditions	DNV, UL, cULus

General information

Outer cable diameter, max.	21 mm	Outer cable diameter, min.	15 mm
O-Ring	NBR	Protection degree with GWDR	IP68 - 5 bar (30 min.), IP69K
Tightening torque	8 Nm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	Yes	Shield diameter, max.	21.00 mm
Shield diameter, min.	13.50 mm	AF size 1	34 mm
AF size 2	34 mm	AF size	34 mm
Protection degree	IP68 - 5 bar (30 min.), IP69K	Cable gland	metric, M 32
Basic material	Brass, nickel-plated	Seal insert	CR
Sealing	NBR	External thread	M 32
Length of thread	8 mm	Torque for cap nut, max.	15.50 Nm
Protection class (UL)	Type 4X	Torque for connecting adapter, max.	8.50 Nm
Torque for connecting adapter, min.	7.50 Nm	Torque for cap nut, min.	14.50 Nm
Clamp insert	Polyamide		


Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		

VG M32 - MS 1/EMV

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

VG M32 - MS 1/EMV

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories



General ordering data

Type	SKMU EMV M32	Version
Order No.	1777650000	SKMU MS EMV (brass locknut - EMC), Locknut, M 32, 4.1 mm, Brass,
GTIN (EAN)	4032248157921	nickel-plated
Qty.	50 ST	

Neoprene flat gasket - GWDR NP



General ordering data

Type	GWDR M32-NP	Version
Order No.	1736260000	GWDR NP (flat gasket - neoprene), Sealing ring, M 32, Neoprene
GTIN (EAN)	4008190956059	
Qty.	50 ST	

Polyethylene flat gasket - GWDR PO



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M32-PO	Version
Order No.	1777960000	GWDR PO (flat gasket - polyethylene), Sealing ring, M 32,
GTIN (EAN)	4032248158225	Polyethylene
Qty.	50 ST	

VG M32 - MS 1/EMV

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Vulcanised fibre gasket - KSWF



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWF M32	Version
Order No.	1076690000	KSWF (flat gasket - vulcanised fibre), Sealing ring, M 32, Vulcanized
GTIN (EAN)	4032248838622	fibre
Qty.	25 ST	

Nylon flat gasket - KSWN



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWN M32	Version
Order No.	1076650000	KSWN (flat gasket - nylon), Sealing ring, M 32, Nylon 6
GTIN (EAN)	4032248838691	
Qty.	25 ST	