

**VG M32-1/K68**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Similar to illustration**



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

**General ordering data**

Version	VG K (standard plastic cable gland), Cable glands, straight, M 32, 10 mm, OD min. 15 - OD max. 21 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	<a href="#">1909880000</a>
Type	VG M32-1/K68
GTIN (EAN)	4032248536801
Qty.	20 items

## VG M32-1/K68

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Height	41 mm	Height (inches)	1.6142 inch
Length	52 mm	Length (inches)	2.0472 inch
Net weight	25.2 g		

## Temperatures

Operating temperature -40 °C...100 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

## Certificate numbers cable gland

Certificate no. cable gland (UL)	E-199260 - BM EN 14	Certificate no. cable gland (cULus)	E-199260 - BM EN 14
Approval conditions	DNV, UL, cULus		

## General information

Outer cable diameter, max.	21 mm	Outer cable diameter, min.	15 mm
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Tightening torque	5 Nm
Silicone	No	UL 94 flammability rating	V-2
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Halogen	Yes
Standards	EN/IEC 62444	AF size 1	36 mm
AF size	36 mm	Protection degree	IP67, IP68 - 5 bar (30 min.)
Cable gland	metric	Basic material	Polyamide 6
Seal insert	CR	External thread	M 32
Length of thread	10 mm	Torque for cap nut, max.	6.50 Nm
Torque for lock nut, min.	4.50 Nm	Note: protection class	IP66 applications only possible with sealing ring for threaded connections. Without sealing ring for threaded connections, only IP54 is possible.
Protection class (UL)	Type 4X	Torque for connecting adapter, max.	5.50 Nm
Torque for connecting adapter, min.	4.50 Nm	Torque for cap nut, min.	5.50 Nm
Torque for lock nut, max.	5.50 Nm		

## Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		

## VG M32-1/K68

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Plastic lock nuts, grey



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	SKMU M32 - K GR	Version	
Order No.	<a href="#">1772480000</a>	SKMU PA (plastic locknut), Locknut, M 32, 7 mm, Polyamid 6 (PA6 -	
GTIN (EAN)	4032248130221	GF30)	
Qty.	100 ST		

### Neoprene flat gasket - GWDR NP



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	GWDR M32-NP	Version	
Order No.	<a href="#">1736260000</a>	GWDR NP (flat gasket - neoprene), Sealing ring, M 32, Neoprene	
GTIN (EAN)	4008190956059		
Qty.	50 ST		

### Polyethylene flat gasket - GWDR PO



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	GWDR M32-PO	Version	
Order No.	<a href="#">1777960000</a>	GWDR PO (flat gasket - polyethylene), Sealing ring, M 32,	
GTIN (EAN)	4032248158225	Polyethylene	
Qty.	50 ST		