

## WSMC 21-25

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

Advantages:

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

### General ordering data

Version	Stainless steel markers, Conductor and cable markers, 131 x 10 mm, silver
Order No.	<a href="#">1912150000</a>
Type	WSMC 21-25
GTIN (EAN)	4032248541195
Qty.	1 items

## WSMC 21-25

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.0197 inch
Height	131 mm	Height (inches)	5.1575 inch
Width	10 mm	Width (inches)	0.3937 inch
Net weight	3 g		

## Temperatures

Operating temperature range	500 °C
-----------------------------	--------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Orientation of print	horizontal	
Number per sheet	1	
Type of printing	To customer specification	
Width	10 mm	
Operating temperature range, max.	500 °C	
Colour	silver	
Basic material	Stainless steel 1.4404	
Printed characters	Mixed characters	
Number of characters	25	
Number of markers per packaging unit	Form of supply	Component part
Number of markers per combination	1 Component part = Conductor and cable markers	
Operating temperature range	500 °C	

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		