

## CLI C 02-33 SDR SG


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

Version	CableLine, Conductor and cable markers, 1.3 - 3 mm, 33 x 3.4 mm, To customer specification
Order No.	<a href="#">1912590000</a>
Type	CLI C 02-33 SDR SG
GTIN (EAN)	4032248542437
Qty.	100 items

## CLI C 02-33 SDR SG

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

Depth	3.5 mm	Depth (inches)	0.1378 inch
Height	33 mm	Height (inches)	1.2992 inch
Width	3.4 mm	Width (inches)	0.1339 inch
Net weight	0.01 g		

## Temperatures

Operating temperature range -30...60 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

## General data

Orientation of print	horizontal	Type of printing	To customer specification
Printing method	Ink jet technology	Version	Loop
Width	3.4 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	60 °C	Operating temperature range, min.	-30 °C
Colour	To customer specification	Halogen	Yes
Basic material	PVC, soft, without Cadmium	Colour of printing	black
Printed characters	To customer specification	Operating temperature range	-30...60 °C
Imprint	Custom printing		

## Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	1.5 mm <sup>2</sup>
Conductor cross-section, min.	0.2 mm <sup>2</sup>	Conductor O.D., max.	3 mm
Conductor O.D., min.	1.3 mm	Conductor O.D.	1.3 - 3 mm
Cross-section for connected wire	0.2 - 1.5 mm <sup>2</sup>		

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**



Similar to illustration