

## CLI C 2-24 SDR SG

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

|            |   |
|------------|---|
| Version    | CableLine, Conductor and cable markers, 4 - 10 mm, 24 x 6.9 mm, To customer specification |
| Order No.  | <a href="#">1912710000</a>  |
| Type       | CLI C 2-24 SDR SG   |
| GTIN (EAN) | 4032248542550   |
| Qty.       | 100 items   |

**CLI C 2-24 SDR SG**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 8 mm   | Depth (inches)  | 0.315 inch  |
| Height     | 24 mm  | Height (inches) | 0.9449 inch |
| Width      | 6.9 mm | Width (inches)  | 0.2717 inch |
| Net weight | 0.01 g |                 |             |

**Temperatures**

Operating temperature range -30...80 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

|                                   |                            |                                   |                           |
|-----------------------------------|----------------------------|-----------------------------------|---------------------------|
| Orientation of print              | horizontal                 | Type of printing                  | To customer specification |
| Printing method                   | Ink jet technology         | Version                           | Loop                      |
| Width                             | 6.9 mm                     | UL 94 flammability rating         | V-0                       |
| Operating temperature range, max. | 80 °C                      | Operating temperature range, min. | -30 °C                    |
| Colour                            | To customer specification  | Halogen                           | Yes                       |
| Basic material                    | PVC, soft, without Cadmium | Colour of printing                | black                     |
| Printed characters                | To customer specification  | Operating temperature range       | -30...80 °C               |
| Imprint                           | Custom printing            |                                   |                           |

**Conductor and cable markers**

|                                  |                          |                               |                    |
|----------------------------------|--------------------------|-------------------------------|--------------------|
| Halogen                          | Yes                      | Conductor cross-section, max. | 16 mm <sup>2</sup> |
| Conductor cross-section, min.    | 2.5 mm <sup>2</sup>      | Conductor O.D., max.          | 10 mm              |
| Conductor O.D., min.             | 4 mm                     | Conductor O.D.                | 4 - 10 mm          |
| Cross-section for connected wire | 2.5 - 16 mm <sup>2</sup> |                               |                    |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**



Similar to illustration