

**CLI C 3-27 SDR SG****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

Version	CableLine, Conductor and cable markers, 8 - 16 mm, 27 x 11 mm, To customer specification
Order No.	<a href="#">1912780000</a>
Type	CLI C 3-27 SDR SG
GTIN (EAN)	4032248542628
Qty.	100 items

## CLI C 3-27 SDR SG

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	17 mm	Depth (inches)	0.6693 inch
Height	27 mm	Height (inches)	1.063 inch
Width	11 mm	Width (inches)	0.4331 inch
Net weight	0.01 g		

## Temperatures

Operating temperature range	-30...60 °C
-----------------------------	-------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Orientation of print	horizontal	Type of printing	To customer specification
Printing method	Ink jet technology	Version	Loop
Width	11 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	60 °C	Operating temperature range, min.	-30 °C
Colour	To customer specification	Halogen	Yes
Basic material	PVC, soft, without Cadmium	Colour of printing	black
Printed characters	To customer specification	Operating temperature range	-30...60 °C
Imprint	Custom printing		

## Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	70 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Conductor O.D., max.	16 mm
Conductor O.D., min.	8 mm	Conductor O.D.	8 - 16 mm
Cross-section for connected wire	16 - 70 mm <sup>2</sup>		

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**



Similar to illustration