

CLI M 2-39 SDR SG**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

Similar to illustration

CLI M identification markers are slid onto CLI MH carrier strips and secured my means of cable ties. The system is particularly suitable for large conductor and cable cross-sections. Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

Version	CableLine, Conductor and cable markers, 10 - 317 mm, 39 x 11.4 mm, yellow
Order No.	1912960000
Type	CLI M 2-39 SDR SG
GTIN (EAN)	4032248542741
Qty.	100 items

CLI M 2-39 SDR SG

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	3 mm	Depth (inches)	0.1181 inch
Height	39 mm	Height (inches)	1.5354 inch
Width	11.4 mm	Width (inches)	0.4488 inch
Net weight	0.01 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	To customer specification				
Printing method	Ink jet technology				
Version	Loop				
Width	11.4 mm				
UL 94 flammability rating	V-0				
Operating temperature range, max.	80 °C				
Operating temperature range, min.	-30 °C				
Colour	yellow				
Halogen	Yes				
Basic material	PVC, soft, without Cadmium				
Colour of printing	black				
Printed characters	To customer specification				
Number of markers per packaging unit	Form of supply	Component part			
Number of markers per combination	1 Component part = Conductor and cable markers				
Operating temperature range	-30...80 °C				
Imprint	Custom printing				

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	500 mm ²
Conductor cross-section, min.	16 mm ²	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor O.D.	10 - 317 mm
Cross-section for connected wire	16 - 500 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

CLI M 2-39 SDR SG

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Similar to illustration