

SF 00/21 MC SDR V2


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

| | |
|------------|--|
| Version | SlimFix, Conductor and cable markers, 1 - 1.3 mm, 21 x 3.2 mm, To customer specification |
| Order No. | 1918530000 |
| Type | SF 00/21 MC SDR V2 |
| GTIN (EAN) | 4032248554218 |
| Qty. | 80 items |

SF 00/21 MC SDR V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 3.2 mm | Depth (inches) | 0.126 inch |
| Height | 21 mm | Height (inches) | 0.8268 inch |
| Width | 3.2 mm | Width (inches) | 0.126 inch |
| Net weight | 0.21 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.002 kg CO2 eq. | |

General data

| | | | |
|--------------------------------------|---|-----------|--|
| Orientation of print | horizontal | | |
| Type of printing | To customer specification | | |
| Printing method | MC Laser | | |
| Width | 3.2 mm | | |
| UL 94 flammability rating | V-2 | | |
| Operating temperature range, max. | 100 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | To customer specification | | |
| Halogen | No | | |
| Basic material | Polyamide 66 | | |
| Colour of printing | black | | |
| Printed characters | Requires M-Print PRO File | | |
| Advice label | Colour based on customer requirements (Please send M-Print PRO file) | | |
| Number of markers per packaging unit | Form of supply | MultiCard | |
| Size of labelling field | 21 x 3.2 mm | | |
| compatible printer | PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2 | | |
| Number of markers per combination | 1 MultiCard = Conductor and cable markers | | |
| Operating temperature range | -40...100 °C | | |

Conductor and cable markers

| | | | |
|----------------------------------|-----------------------------|-------------------------------|----------------------|
| Halogen | No | Conductor cross-section, max. | 0.25 mm ² |
| Conductor cross-section, min. | 0.25 mm ² | Conductor O.D., max. | 1.3 mm |
| Conductor O.D., min. | 1 mm | Conductor O.D. | 1 - 1.3 mm |
| Cross-section for connected wire | 0.25 - 0.25 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |