


SF 6/21 MC SDR V2

Weidmüller Interface GmbH & Co. KG

Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Version	SlimFix, Conductor and cable markers, 5.8 - 7.8 mm, 21 x 8.4 mm, To customer specification
Order No.	1919160000
Type	SF 6/21 MC SDR V2
GTIN (EAN)	4032248555482
Qty.	32 items

SF 6/21 MC SDR V2

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	8.5 mm	Depth (inches)	0.3346 inch
Height	21 mm	Height (inches)	0.8268 inch
Width	8.4 mm	Width (inches)	0.3307 inch
Net weight	0.69 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
Product Carbon Footprint	Cradle to gate 0.009 kg CO2 eq.

General data

Orientation of print	horizontal
Type of printing	To customer specification
Printing method	MC Laser
Width	8.4 mm
UL 94 flammability rating	V-2
Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C
Colour	To customer specification
Halogen	No
Basic material	Polyamide 66
Colour of printing	black
Printed characters	Requires M-Print PRO File
Advice label	Colour based on customer requirements (Please send M-Print PRO file)
Number of markers per packaging unit	Form of supply MultiCard
Size of labelling field	21 x 8.4 mm
compatible printer	PRINTJET CONNECT, MCP BASIC 2, MCP PLUS 2
Number of markers per combination	1 MultiCard = Conductor and cable markers
Operating temperature range	-40...100 °C

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	10 mm ²	Conductor O.D., max.	7.8 mm
Conductor O.D., min.	5.8 mm	Conductor O.D.	5.8 - 7.8 mm
Cross-section for connected wire	10 - 16 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		