


ZQV 4/20 GE**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Z-series, Cross-connector, For the terminals, Number of poles: 20
Order No.	1909010000
Type	ZQV 4/20 GE
GTIN (EAN)	4032248535637
Qty.	20 items

ZQV 4/20 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	31.6 mm	Depth (inches)	1.2441 inch
Height	120.3 mm	Height (inches)	4.7362 inch
Width	2.8 mm	Width (inches)	0.1102 inch
Net weight	18.2 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-60 °C...85 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.236 kg CO2 eq.	

Material data

Basic material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Type of fixing	Plugged	Installation advice	Direct mounting
Explosion-tested version	No		

Dimensions

Pitch in mm (P)	6.10 mm
-----------------	---------

General

Number of poles	20	Installation advice	Direct mounting
-----------------	----	---------------------	-----------------

Rating data

Rated voltage	400 V	Nominal current	32 A
---------------	-------	-----------------	------

Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements. The usage of cross connectors reduces the rated voltage to 400 V. The voltage reduced to 25 V if cut cross connection with blank cut edges are used. Cross connections with >10 poles have bare cut edges ex works.
---------------------	--

Technical data

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		