

**SAISM-M8-4P(TL)****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M8 round plug-in connectors are particularly suited to applications where space is limited. The solder connection provides high contact density on a small area. With this technology the stripped conductor is soldered to the contacts, producing good electrical conductivity.

**General ordering data**

Version	Field attachable connector, M8
Order No.	<a href="#">1921040000</a>
Type	SAISM-M8-4P(TL)
GTIN (EAN)	4032248562480
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2025-05-30T00:00:00+02:00
Alternative product	<a href="#">SAISGS-M-4A-3.5/5.5-M8-IF</a>

## SAISM-M8-4P(TL)

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E307231

## Dimensions and weights

Net weight 20 g

## Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1, Imidazolidine-2-thione 96-45-7

SCIP bcee35cf-c0f5-43d2-8daf-65ab0d08641a

## Technical data customisable plug-in connectors

Number of poles	4	Coding	none
Contact surface	Gold-plated	Type of connection	Solder connection
Housing main material	CuZn	Insulation resistance	108 Ω
Cable diameter, max.	5 mm	Cable diameter, min.	3.5 mm
Conductor cross-section, max.	0.25 mm <sup>2</sup>	Conductor cross-section, min.	0.14 mm <sup>2</sup>
Nominal voltage	60 V	Nominal current	4 A
Protection degree	IP67	Plugging cycles	≥ 100
Pollution severity	3	Gender of contact	Male
Shield connection	Yes	Threaded ring material	Diecast zinc
Temperature range of housing	-40 ... +85 °C		

## Standards

Connector standard IEC 61076-2-104

## Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 9.0	27-44-01-02
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-02
ECLASS 11.0	27-44-01-02	ECLASS 12.0	27-44-01-16
ECLASS 13.0	27-44-01-02	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		