

VG H M25 MS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

| | |
|-----------------|--|
| Version | VG H (HDC halved cable gland), Cable glands, straight, M 25, 8 mm, OD min. 8.5 - OD max. 18 mm, IP65, Brass, nickel-plated |
| Order No. | 1921740000 |
| Type | VG H M25 MS |
| GTIN (EAN) | 4032248563012 |
| Qty. | 25 items |
| Delivery status | Discontinued |
| Available until | 2024-08-31T00:00:00+02:00 |

VG H M25 MS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Height | 11.5 mm | Height (inches) | 0.4528 inch |
| Width | 25 mm | Width (inches) | 0.9842 inch |
| Net weight | 18.76 g | | |

Temperatures

| | |
|-----------------------|----------------|
| Operating temperature | -20 °C...60 °C |
|-----------------------|----------------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | b5ff1f66-ddba-4739-9fc0-0521ddb52139 |

General information

| | | | |
|--------------------------------------|--------------|--------------------------------------|----------------------|
| Outer cable diameter, max. | 18 mm | Outer cable diameter, min. | 8.5 mm |
| O-Ring | NBR | Protection degree with GWDR | IP65 |
| Operating temperature range, max. | 60 °C | Operating temperature range, min. | -20 °C |
| Pitch of thread | 1.5 mm | Halogen | Yes |
| AF size 1 | 25 mm | AF size 2 | 25 mm |
| AF size | 25 mm | Protection degree | IP65 |
| Cable gland | metric, M 25 | Basic material | Brass, nickel-plated |
| Seal insert | NBR | Sealing | NBR |
| Notch multi-layer sealing diameter 1 | 8.5 mm | Notch multi-layer sealing diameter 2 | 11.5 mm |
| Notch multi-layer sealing diameter 3 | 14.5 mm | Notch multi-layer sealing diameter 4 | 18 mm |
| External thread | M 25 | Length of thread | 8 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000441 | ETIM 9.0 | EC000441 |
| ETIM 10.0 | EC000441 | ECLASS 14.0 | 27-14-08-01 |
| ECLASS 15.0 | 27-14-08-01 | | |