

## VG M16-1/K68

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

### General ordering data

Version	VG K (standard plastic cable gland), Cable glands, straight, M 16, 8 mm, OD min. 4 - OD max. 8 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	<a href="#">1909860000</a>
Type	VG M16-1/K68
GTIN (EAN)	4032248536788
Qty.	50 items

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Height	26.5 mm	Height (inches)	1.0433 inch
Length	34.5 mm	Length (inches)	1.3583 inch
Net weight	6.44 g		

**Temperatures**

Operating temperature -40 °C...100 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
REACH SVHC No SVHC above 0.1 wt%

**Certificate numbers cable gland**

Certificate no. cable gland (UL)	E-199260 - BM EN 11	Certificate no. cable gland (cULus)	E-199260 - BM EN 11
Approval conditions	DNV, UL, cULus		

**General information**

Outer cable diameter, max.	8 mm	Outer cable diameter, min.	4 mm
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Tightening torque	2.5 Nm
Silicone	No	UL 94 flammability rating	V-2
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Halogen	Yes
Standards	EN/IEC 62444	AF size 1	19 mm
AF size	22 mm	Protection degree	IP67, IP68 - 5 bar (30 min.)
Cable gland	metric	Basic material	Polyamide 6
Seal insert	CR	External thread	M 16
Length of thread	8 mm	Torque for cap nut, max.	3.00 Nm
Torque for lock nut, min.	2.00 Nm	Note: protection class	IP66 applications only possible with sealing ring for threaded connections. Without sealing ring for threaded connections, only IP54 is possible.
Protection class (UL)	Type 4X	Torque for connecting adapter, max.	3.00 Nm
Torque for connecting adapter, min.	2.00 Nm	Torque for cap nut, min.	2.00 Nm
Torque for lock nut, max.	3.00 Nm		

**Classifications**

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		