

## VG M40-1/MS68

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

### General ordering data

Version	VG MS (standard brass cable gland), Cable glands, straight, M 40, 9 mm, OD min. 19 - OD max. 28 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Brass, nickel-plated
Order No.	<a href="#">1909940000</a>
Type	VG M40-1/MS68
GTIN (EAN)	4032248536863
Qty.	10 items

## VG M40-1/MS68

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Height	43.5 mm	Height (inches)	1.7126 inch
Length	52.5 mm	Length (inches)	2.0669 inch
Net weight	76.1 g		

## Temperatures

Operating temperature -40 °C...100 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

## Certificate numbers cable gland

Certificate no. cable gland (GERMLLOYD)	E-14047	Certificate no. cable gland (UL)	E-199260
Certificate no. cable gland (cULus)	E-199260	Approval conditions	DNV, UL, cULus

## General information

Outer cable diameter, max.	28 mm	Outer cable diameter, min.	19 mm
O-Ring	NBR	Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Tightening torque	12 Nm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	Yes	AF size 1	43 mm
AF size 2	43 mm	AF size	43 mm
Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Cable gland	metric, M 40
Basic material	Brass, nickel-plated	Seal insert	CR
Sealing	NBR	External thread	M 40
Length of thread	9 mm	Torque for cap nut, max.	18.00 Nm
Protection class (UL)	Type 4X	Torque for connecting adapter, max.	12.50 Nm
Torque for connecting adapter, min.	11.50 Nm	Torque for cap nut, min.	16.00 Nm
Clamp insert	Polyamide		

## Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		

## VG M40-1/MS68

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Accessories

### Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	SKMU M40 MS	Version	
Order No.	<a href="#">1737030000</a>	SKMU MS (brass locknut), Locknut, M 40, 5 mm, Brass, nickel-plated	
GTIN (EAN)	4008190956509		
Qty.	50 ST		

### Brass lock nuts, natural finish



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	SKMU M40 MS SC	Version	
Order No.	<a href="#">0930640005</a>	SKMU MS (brass locknut), Locknut, M 40, 4.8 mm, Brass	
GTIN (EAN)	4032248976096		
Qty.	10 ST		

### Neoprene flat gasket - GWDR NP



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	GWDR M40-NP	Version	
Order No.	<a href="#">1736270000</a>	GWDR NP (flat gasket - neoprene), Sealing ring, M 40, Neoprene	
GTIN (EAN)	4008190956066		
Qty.	20 ST		

**Accessories****Polyethylene flat gasket - GWDR PO**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	GWDR M40-PO	Version	
Order No.	<a href="#">1777970000</a>	GWDR PO (flat gasket - polyethylene), Sealing ring, M 40,	
GTIN (EAN)	4032248 158232	Polyethylene	
Qty.	50 ST		