



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image















1







PCB terminal for fully automatic assembly in reflow soldering (SMT), with Push In conductor connection system. Conductor inserted and slider operated in same direction (TOP). Packed in box or as tape on reel. Pin lengths optimised at 1.5 mm or 3.5 mm.

General ordering data

, , , , , , , , , , , , , , , , , , , ,		
ber of poles: 5, 90°, Solder pin length (I): 1.5 mm black, PUSH IN with push button, Clamping rang max.: 1.5 mm², Tape Order No. 1924880000 Type LSF-SMT 5.00/05/90 1.5SN BK RL GTIN (EAN) 4032248565030 Oty. 265 items Product data IEC: 500 V / 17.5 A / 0.2 - 1.5 mm² UL: 300 V / 12 A / AWG 28 - AWG 14		
Type LSF-SMT 5.00/05/90 1.5SN BK RL GTIN (EAN) 4032248565030 Qty. 265 items Product data IEC: 500 V / 17.5 A / 0.2 - 1.5 mm² UL: 300 V / 12 A / AWG 28 - AWG 14	Version	ber of poles: 5, 90°, Solder pin length (I): 1.5 mm, black, PUSH IN with push button, Clamping range,
GTIN (EAN) 4032248565030 Oty. 265 items Product data IEC: 500 V / 17.5 A / 0.2 - 1.5 mm² UL: 300 V / 12 A / AWG 28 - AWG 14	Order No.	<u>1924880000</u>
Oty. 265 items Product data IEC: 500 V / 17.5 A / 0.2 - 1.5 mm² UL: 300 V / 12 A / AWG 28 - AWG 14	Туре	LSF-SMT 5.00/05/90 1.5SN BK RL
Product data IEC: 500 V / 17.5 A / 0.2 - 1.5 mm ² UL: 300 V / 12 A / AWG 28 - AWG 14	GTIN (EAN)	4032248565030
UL: 300 V / 12 A / AWG 28 - AWG 14	Qty.	265 items
Packaging Tape	Product data	· ·
	Packaging	Tape





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	<u>UL Website</u>
Certificate No. (cURus)	F60693

Dimensions and weights

Depth	14.75 mm	Depth (inches)	0.5807 inch
Height	10 mm	Height (inches)	0.3937 inch
Height of lowest version	8.5 mm	Width	24.2 mm
Width (inches)	0.9528 inch	Net weight	4.04 g

Temperatures

Continuous operating temp., max. 120 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

System parameters

Product family	OMNIMATE Signal - series LSF	Wire connection method	PUSH IN with push button
Mounting onto the PCB	THT/THR solder connection	Conductor outlet direction	90°
Pitch in mm (P)	5.00 mm	Pitch in inches (P)	0.197 "
Number of poles	5	Pin series quantity	1
Fitted by customer	No	Number of rows	1
Solder pin length (I)	1.5 mm	Solder pin length tolerance	0 / -0.3 mm
Solder pin dimensions	0.35 x 0.8 mm	Solder pin dimensions = d tolerance	0 / -0.1 mm
Solder eyelet hole diameter (D)	1.1 mm	Solder eyelet hole diameter tolerance (I	D)+ 0,1 mm
Number of solder pins per pole	2	Stripping length	8 mm
L1 in mm	20.00 mm	L1 in inches	0.788 "
Touch-safe protection acc. to DIN VDE 0470	IP 20	Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch
Protection degree	IP20	Volume resistance	1.60 mΩ

Material data

Insulating material	LCP GF	Colour	black
Colour chart (similar)	RAL 9011	Insulating material group	Illa
Comparative Tracking Index (CTI)	≥ 175	Moisture Level (MSL)	1
UL 94 flammability rating	V-0	Contact material	Copper alloy
Layer structure of solder connection	46 µm Sn matt	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	120 °C	Temperature range, installation, min.	-30 °C
Temperature range, installation, max.	120 °C		





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data


AI 4		
Conductors	SUITABLE TOP	connection

Conductors suitable for conn	ection		
Clamping range, min.	0.13 mm ²		
Clamping range, max.	1.5 mm ²		
Wire connection cross section AWG, min.	AWG 28		
Wire connection cross section AWG,	AWG 14		
max.			
Solid, min. H05(07) V-U	0.2 mm ²		
Solid, max. H05(07) V-U	1.5 mm ²		
Flexible, min. H05(07) V-K	0.2 mm ²		
Flexible, max. H05(07) V-K	1.5 mm ²		
w. plastic collar ferrule, DIN 46228 pt min.	4, 0.25 mm²		
w. plastic collar ferrule, DIN 46228 pt max.	4, 0.75 mm²		
w. wire end ferrule, DIN 46228 pt 1,	0.25 mm²		
min.			
w. wire end ferrule, DIN 46228 pt 1, max.	1.5 mm ²		
Clampable conductor	Cross-section for conductor connection	Туре	fine-wired
		nominal	0.25 mm ²
	wire end ferrule	Stripping length	nominal 10 mm
		Recommended wire- end ferrule	H0,25/12 HBL
	Cross-section for conductor connection	Туре	fine-wired
		nominal	0.34 mm ²
	wire end ferrule	Stripping length	nominal 10 mm
		Recommended wire- end ferrule	H0,34/12 TK
	Cross-section for conductor connection	Туре	fine-wired
		nominal	0.5 mm ²
	wire end ferrule	Stripping length	nominal 10 mm
		Recommended wire- end ferrule	H0,5/14 OR
	Cross-section for conductor connection	Туре	fine-wired
		nominal	0.75 mm ²
	wire end ferrule	Stripping length	nominal 10 mm
		Recommended wire- end ferrule	H0,75/14T HBL
Reference text	Length of ferrules is to be chosen depending of diameter of the plastic collar should not be larger	on the product and the rate	d voltage., The outside

Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 60947-7-4	Rated current, min. number of poles (Tu=20°C)	17.5 A
Rated current, max. number of poles (Tu=20°C)	17.5 A	Rated current, min. number of poles (Tu=40°C)	17.5 A
Rated current, max. number of poles (Tu=40°C)	15 A	Rated voltage for surge voltage class / pollution degree II/2	500 V
Rated voltage for surge voltage class / pollution degree III/2	320 V	Rated voltage for surge voltage class / pollution degree III/3	250 V
Rated impulse voltage for surge voltage class/ pollution degree II/2	4 kV	Rated impulse voltage for surge voltage class/ pollution degree III/2	4 kV
Rated impulse voltage for surge voltage class/ contamination degree III/3	4 kV	Short-time withstand current resistance	3 x 1s with 80 A







Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Rated data acc. to CSA

Institute (CSA)	CSA	Certificate No. (CSA)	200039-1664286
Rated voltage (Use group B / CSA)	300 V	Rated voltage (Use group D / CSA)	300 V
Rated current (Use group B / CSA)	10 A	Rated current (Use group D / CSA)	10 A
Wire cross-section, AWG, min.	AWG 28	Wire cross-section, AWG, max.	AWG 14
Reference to approval values	Specifications are maximum values, details - see approval certificate.		

Rated data acc. to UL 1059

Institute (cURus)	CURUS	Certificate No. (cURus)	E60693
Rated voltage (Use group B / UL 1059)	300 V	Rated voltage (Use group D / UL 1059)	300 V
Rated current (Use group B / UL 1059)	12 A	Rated current (Use group D / UL 1059)	10 A
Wire cross-section, AWG, min.	AWG 28	Wire cross-section, AWG, max.	AWG 14
Reference to approval values	Specifications are maximum values, details - see approval certificate.		

Packing

ESD Level packaging	static dissipative	Packaging	Tape
VPE length	356.00 mm	VPE width	337.00 mm
VPE height	78.00 mm	Tape depth (T2)	13.00 mm
Tape width (W)	44 mm	Tape pocket depth (K0)	12.50 mm
Tape pocket height (A0)	14.40 mm	Tape pocket width (B0)	24.50 mm
Tape pocket separation (P1)	20.00 mm	Tape hole separation (E)	1.75 mm
Tape pocket separation (F)	20.20 mm	Tape reel diameter Ø (A)	330 mm
Surface resistance	Rs = 109 - 1012 Ω		

Type tests

Test: Durability of markings	Standard	DIN EN 60512-1-1 / 01.03	
	Test	mark of origin, type identification, pitch, approva marking UL, durability	
	Evaluation	available	
Test: Clampable cross section	Standard	DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 12.02	
	Conductor type	Type of conductor solid 0.14 mm ² and conductor cross-section	
		Type of conductor stranded 0.14 mm ² and conductor cross-section	
		Type of conductor solid 1.5 mm ² and conductor cross-section	
		Type of conductor stranded 1.5 mm ² and conductor cross-section	
		Type of conductor AWG 24/1 and conductor cross-section	
		Type of conductor AWG 26/19 and conductor cross-section	
		Type of conductor AWG 16/1 and conductor cross-section	

Creation date 08.11.2025 08:29:19 MEZ





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

		Type of conductor AWG 16/19 and conductor cross-section		
	Evaluation	passed		
Test for damage to and accidental	Standard	DIN EN 60999-1 section 9.4 / 12.00		
oosening of conductors	Requirement	0.2 kg		
	Conductor type	Type of conductor AWG 24/1 and conductor cross-section		
		Type of conductor AWG 24/19 and conductor cross-section		
	Requirement	0.3 kg		
	Conductor type	Type of conductor stranded 0.25 mm ² and conductor cross-section		
		Type of conductor solid 0.5 mm ² and conductor cross-section		
	Evaluation	passed		
	Requirement	0.4 kg		
	Conductor type	Type of conductor solid 1.5 mm ² and conductor cross-section		
		Type of conductor stranded 1.5 mm ² and conductor cross-section		
		Type of conductor AWG 16/1 and conductor cross-section		
		Type of conductor AWG 16/19 and conductor cross-section		
	Evaluation	passed		
Pull-out test	Standard	DIN EN 60999-1 section 9.5 / 12.00		
	Requirement	≥10 N		
	Conductor type	Type of conductor AWG 24/1 and conductor cross-section		
		Type of conductor AWG 24/19 and conductor cross-section		
	Evaluation	passed		
	Requirement	≥20 N		
	Conductor type	Type of conductor stranded 0.25 mm ² and conductor cross-section		
		Type of conductor H05V-K0.5 and conductor cross-section		
	Evaluation	passed		
	Requirement	≥40 N		
	Conductor type	Type of conductor H07V-U1.5 and conductor cross-section		
		Type of conductor H07V-K1.5 and conductor cross-section		
		Type of conductor AWG 16/1 and conductor cross-section		





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

	Type of conductor and conductor cross-section	AWG 16/19
Evaluation	passed	

Important note

IPC conformity

Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

• Additional push button colours on request

- Operating force of slider max. 40 N
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule with plastic collar to DIN 46228/4
- Wire end ferrule without plastic collar to DIN 46228/1
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- Crimping shape "A" for wire end ferrules with PZ 6/5 crimping tool recommended.
- Long term storage of the product with average temperature of 50 $^{\circ}\text{C}$ and maximum humidity 70%, 36 months

Classifications

ETIM 6.0	EC002643	ETIM 7.0	EC002643
ETIM 8.0	EC002643	ETIM 9.0	EC002643
ETIM 10.0	EC002643	ECLASS 9.0	27-44-04-01
ECLASS 9.1	27-44-04-01	ECLASS 10.0	27-44-04-01
ECLASS 11.0	27-46-01-01	ECLASS 12.0	27-46-01-01
ECLASS 13.0	27-46-01-01	ECLASS 14.0	27-46-01-01
ECLASS 15.0	27-46-01-01		

Weidmüller **₹**

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com


Drawings

Product image





LSF-SMT 5.00/05/90 1.5SN BK RL

Dimensional drawing



Graph Graph





Weidmüller **3**

LSF-SMT 5.00/05/90 1.5SN BK RL


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany


www.weidmueller.com

Drawings


Dimensional drawing



Dimensional drawing



DIRECTION OF UNREELING





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Slotted screwdriver



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Туре	SDIS 0.4X2.5X75	Version
Order No.	9008370000	Screwdriver, Screwdriver
GTIN (EAN)	4032248056330	
Qty.	1 ST	
Туре	SDS 0.4X2.5X75	Version
Type Order No.	SDS 0.4X2.5X75 9009030000	Version Screwdriver, Screwdriver