

## WSM SERVICE BOX KOMP.

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

Advantages:

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

### General ordering data

|            |  |
|------------|--|
| Version    | Stainless steel markers, Conductor and cable markers, 330 x 174 mm, silver |
| Order No.  | <a href="#">1924930000</a>   |
| Type       | WSM SERVICE BOX KOMP.  |
| GTIN (EAN) | 4032248565160  |
| Qty.       | 1 items  |

## WSM SERVICE BOX KOMP.

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |        |                 |              |
|------------|--------|-----------------|--------------|
| Depth      | 109 mm | Depth (inches)  | 4.2913 inch  |
| Height     | 330 mm | Height (inches) | 12.9921 inch |
| Width      | 174 mm | Width (inches)  | 6.8504 inch  |
| Net weight | 1169 g |                 |              |

### Temperatures

|                             |        |
|-----------------------------|--------|
| Operating temperature range | 250 °C |
|-----------------------------|--------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General data

|                                      |  |                |
|--------------------------------------|--|----------------|
| Orientation of print                 | horizontal                                     |                |
| Type of printing                     | Standard                                       |                |
| Width                                | 174 mm   |                |
| Operating temperature range, max.    | 250 °C   |                |
| Colour                               | silver   |                |
| Basic material                       | Stainless steel 1.4404                         |                |
| Printed characters                   | Mixed characters                               |                |
| Number of markers per packaging unit | Form of supply                                 | Component part |
| Number of markers per combination    | 1 Component part = Conductor and cable markers |                |
| Operating temperature range          | 250 °C   |                |
| Imprint                              | see text                                       |                |

### Conductor and cable markers

|                                  |                          |                               |                    |
|----------------------------------|--------------------------|-------------------------------|--------------------|
| Conductor cross-section, max.    | 500 mm <sup>2</sup>      | Conductor cross-section, min. | 16 mm <sup>2</sup> |
| Cross-section for connected wire | 16 - 500 mm <sup>2</sup> |                               |                    |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |