

**WSMC 1-5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

**Advantages:**

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

**General ordering data**

Version	Stainless steel markers, Conductor and cable markers, 53.5 x 10 mm, silver
Order No.	<a href="#">1912170000</a>
Type	WSMC 1-5
GTIN (EAN)	4032248541218
Qty.	100 items

## WSMC 1-5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.0197 inch
Height	53.5 mm	Height (inches)	2.1063 inch
Width	10 mm	Width (inches)	0.3937 inch
Net weight	0.08 g		

## Temperatures

Operating temperature range	500 °C
-----------------------------	--------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Orientation of print	horizontal	
Type of printing	To customer specification	
Width	10 mm	
Operating temperature range, max.	500 °C	
Colour	silver	
Basic material	Stainless steel 1.4404	
Printed characters	Mixed characters	
Number of characters	5	
Number of markers per packaging unit	Form of supply	Component part
Number of markers per combination	1 Component part = Conductor and cable markers	
Operating temperature range	500 °C	
Number per roll	20	

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02
ECLASS 13.0	27-28-11-02	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		