

**CLI C 3-36 SDR SG****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|            |  |
|------------|--|
| Version    | CableLine, Conductor and cable markers, 8 - 16 mm, 36 x 11 mm, To customer specification |
| Order No.  | <a href="#">1912810000</a>   |
| Type       | CLI C 3-36 SDR SG  |
| GTIN (EAN) | 4032248542659  |
| Qty.       | 100 items  |

## CLI C 3-36 SDR SG

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |       |                 |             |
|------------|-------|-----------------|-------------|
| Depth      | 17 mm | Depth (inches)  | 0.6693 inch |
| Height     | 36 mm | Height (inches) | 1.4173 inch |
| Width      | 11 mm | Width (inches)  | 0.4331 inch |
| Net weight | 4.5 g |                 |             |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...60 °C |
|-----------------------------|-------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General data

|                                   |                            |                                   |                           |
|-----------------------------------|----------------------------|-----------------------------------|---------------------------|
| Orientation of print              | horizontal                 | Type of printing                  | To customer specification |
| Printing method                   | Ink jet technology         | Version                           | Loop                      |
| Width                             | 11 mm                      | UL 94 flammability rating         | V-0                       |
| Operating temperature range, max. | 60 °C                      | Operating temperature range, min. | -30 °C                    |
| Colour                            | To customer specification  | Halogen                           | Yes                       |
| Basic material                    | PVC, soft, without Cadmium | Colour of printing                | black                     |
| Printed characters                | To customer specification  | Operating temperature range       | -30...60 °C               |
| Imprint                           | Custom printing            |                                   |                           |

### Conductor and cable markers

|                                  |                         |                               |                    |
|----------------------------------|-------------------------|-------------------------------|--------------------|
| Halogen                          | Yes                     | Conductor cross-section, max. | 70 mm <sup>2</sup> |
| Conductor cross-section, min.    | 16 mm <sup>2</sup>      | Conductor O.D., max.          | 16 mm              |
| Conductor O.D., min.             | 8 mm                    | Conductor O.D.                | 8 - 16 mm          |
| Cross-section for connected wire | 16 - 70 mm <sup>2</sup> |                               |                    |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**



Similar to illustration