



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com













1

Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

| Version | Sensor/actuator line, Connecting line, M12 / M12, Number of poles : 5, 10 m, pin, straight - socket, straight, Shielded: No, LED: No, Sheath material: PVC, Halogen: Yes |
|------------|---|
| Order No. | <u>1925321000</u> |
| Туре | SAIL-M12GM12G-5-10V |
| GTIN (EAN) | 4032248567645 |
| Qty. | 1 items |
| | |





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

| Aр | pr | ov | a | s |
|----|----|----|---|---|
|----|----|----|---|---|

| Approvals | 440 |
|-----------|------------|
| | C C (UL)us |
| | LISTED |

| ROHS | Conform |
|-------------------------|-------------------|
| UL File Number Search | <u>UL Website</u> |
| Certificate no. (cULus) | F307231 |

Dimensions and weights

Net weight 501 g

Environmental Product Compliance

| RoHS Compliance Status | Compliant with exemption |
|--------------------------------------|--------------------------------------|
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 1c533b66-fcff-4da5-b89f-fd55fbf5cb55 |

Technical specifications for cable

| Cable length | 10 m | Sheathing colour | black |
|-----------------------------|-------|--|---------------------------------|
| Suitable for cable carriers | No | Core cross-section | 0.34 mm ² |
| Shielded | No | Halogen | Yes |
| Insulation | PVC | Sheath material | PVC |
| Configurable cable length | No | Outer cladding in accordance with UL AWM style | 2464 (80 °C / 300 V) |
| Hybrid cable | No | Irradiation crosslinked | No |
| Welding spark resistance | No | Colour coding | brown, white, blue, black, grey |
| Torsion resistance | 0 °/m | Temperature range, stationary | -3080 °C |
| Resistant to welding beads | No | Temperature range, moving | -580 °C |
| Number of poles | 5 | Outside diameter | 5.7 mm ± 0.1 mm |

General technical data

| Coding | A-coded | Connection thread | M12 / M12 |
|------------------------------|-------------------------------------|------------------------|--|
| Contact surface | Gold-plated | LED | No |
| Version | pin, straight - socket, straight | Housing main material | PUR |
| Insulation resistance | 108 Ω | Contact material | CuZn35PB2 |
| Nominal voltage | 60 V | Nominal current | 4 A |
| AF size | 12 mm | Protection degree | IP65, IP66, IP67, IP68, when screwed in |
| Plugging cycles | ≥ 100 | Pollution severity | 3 |
| jumpered | No | Threaded ring material | Diecast zinc |
| Temperature range of housing | -25+85 °C | Tightening torque | M12: 0.8 - 1.2 Nm |

Electrical properties

| Insulation resistance | 108 Ω | Nominal voltage | 60 V |
|-----------------------|-------|-----------------|------|

General standards

| Connector standard | IEC 61076-2-101 | Certificate no. (cULus) | E307231 |
|--------------------|-----------------|-------------------------|---------|

Catalogue status / Drawings 2





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

| Standards | | |
|--------------------|--|--|
| Connector standard | IEC 61076-2-101 | |
| Plug, left | | |
| Plug left | connector, M12, A-coded, Number of poles: 5, male contact, straight, unshielded | |
| Plug, right | | |
| Plug right | connector, M12, A-coded, Number of poles: 5, female contact, straight, unshielded | |

Classifications

| Classifications | | | |
|-----------------|-------------|-------------|-------------|
| | | | |
| ETIM 6.0 | EC001855 | ETIM 7.0 | EC001855 |
| ETIM 8.0 | EC001855 | ETIM 9.0 | EC001855 |
| ETIM 10.0 | EC001855 | ECLASS 9.0 | 27-06-03-11 |
| ECLASS 9.1 | 27-06-03-11 | ECLASS 10.0 | 27-06-03-11 |
| ECLASS 11.0 | 27-06-03-11 | ECLASS 12.0 | 27-06-03-11 |
| ECLASS 13.0 | 27-06-03-11 | ECLASS 14.0 | 27-06-03-11 |
| ECLASS 15.0 | 27-06-03-11 | | |

Catalogue status / Drawings



Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26 D-32758 Detmold Germany


www.weidmueller.com

Drawings

Dimensioned drawing









Male, straight

Straight socket

Pole scheme

Pole scheme









Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Drawings

Wiring diagram

The ideal tool: Screwty ® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F